



TECHNICAL DATA SHEET

Document number: TTDS-033
Issue: 7
Date: August 2014

HS/HC Heat shrinkable sleeves

MATERIAL DESCRIPTION:

Thin wall, flame retarded radiation cross-linked polyolefin heat-shrinkable tubing, assembled as organized cut sleeves on a paper carrier.
HS products are 2:1 shrink ratio. HC products are 3:1 shrink ratio.

USE:

Identification of wires and cables by computer-based printing onto sleeves. Suited to a wide variety of applications, including those with military standard requirements.

PRINTING SYSTEM

Print Quality and Print Performance can only be guaranteed when specific TE printer and ribbons are used.
The current list of printers and ribbons can be found in TE document 411-121005 'Identification Printer Product Ribbon Matrix'

This document can be found at the TE document centre:
<http://www.te.com/commerce/DocumentDelivery/DDEController>

Cable markers are fully supported by WINTOTAL and PrintEasy label printing software, available from the TE product store:
<http://www.te.com/en/general/label-printing-software.html>
Contact a TE representative for further information

SPECIFICATIONS/APPROVALS:

TE Specification RW-2539

2:1 shrink ratio AMS-DTL-23053/C Class 1 (2:1),
3:1 shrink ratio AMS-DTL-23053/C Class 1 except dimensions.

SERVICE TEMPERATURE:

-55°C to +135°C (-67°F to +275°F).

MINIMUM SHRINK TEMPERATURE:

120°C (248°F).

SHELF LIFE:

Five years from date of manufacture. See TE document 408-121006 for guidance.

COLOURS:

White or yellow. Other colours available on request.

If the document is printed it becomes uncontrolled
Check with TE Connectivity (TE) for latest version

Author: L Smith
Issue date: August 2014
Page: 1 of 2

While TE Connectivity Ltd. has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.



TECHNICAL DATA SHEET

Document number: TTDS-033
Issue: 7
Date: August 2014

HS/HC Heat shrinkable sleeves

FLAMMABILITY:	Self-extinguishing, non-flame propagating (ASTM D2671 Procedure B).	
TENSILE STRENGTH:	18 MPa typical (ASTM D638).	
ULTIMATE ELONGATION:	450% typical (ASTM D638).	
DIELECTRIC STRENGTH:	20MV/m minimum (ASTM D2671).	
VOLUME RESISTIVITY	10 ¹⁴ ohm-cm minimum (ASTM D876)	
WATER ABSORPTION:	0.1% typical (ASTM D570).	
HEAT SHOCK:	400% typical UE retained after 168 hours at 158°C (316°F). No cracking, dripping or flowing after 4 hours at 250°C (392°F).	
LOW TEMPERATURE FLEX:	No cracking or splitting after 4 hours at -55°C (-65°F) (ASTM D 2671).	
PRINT PERFORMANCE:	SAE AS5942, 20 rubs, 1Kg load	Legible, minimum print contrast 3
	MIL 202 METHOD 215, Solvents A, B, D, 30 strokes, tooth brush	Legible, minimum print contrast 3
	MIL STD 23053/5C, Resistance to fluids, 24 hours at 23°C (75°F), Crockmeter 20 rubs, 1kg load.	Legible, minimum print contrast 3
	BS 4G 198: Pt 3, Resistance to fluids, 24 hours, 25 wipes with tissue.	Legible, minimum print contrast 3

Further information and availability can be found through the TE Cable Identification web site:
<http://www.te.com/catalog/labels-identification/menu/en/12933?BML=10576>

If the document is printed it becomes uncontrolled
Check with TE Connectivity (TE) for latest version

Author: L Smith
Issue date: August 2014
Page: 2 of 2

While TE Connectivity Ltd. has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this document are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.