


POTTING BOXES

Order data on page 173

OKW
GEHÄUSE
SYSTEME



FOR EASY ENCAPSULATION

Sizes (L x W x H in mm)

Duroplast
20 x 20 x 13.1 – 100 x 100 x 40

PA 6.6
14 x 14 x 11.5 – 46.2 x 46.2

ABS
12.3 x 12.3 x 15.3 – 67.5 x 35.8 x 46.3

THE PRODUCT

OKW POTTING BOXES – a comprehensive range of boxes for potting electronic assemblies. With special cost advantages for series-type production.

Potted assemblies are protected from shock as well as temperature, dampness and chemical influences. The versions made of Duroplast are less resistant to impact than the Polyamide 6.6 or ABS models.

YOUR ADVANTAGE

Duroplast
Resistant to deformation and extreme temperatures.

Polyamide 6.6
Good value for money. High-impact.




ABS
Good value for money. Preferably for potting small assemblies.



detailed drawings see our website
www.okw.com


POTTING BOXES*1

POTTING BOXES	Article	Outside dim. in mm			Wall thickness in mm	Version	Part-No.	
		L	W	H			case	lid
	Duroplast	20	20	13.1	0.85	I	A 80 20 130	—
		25	25	14.8	0.8	I	A 80 25 150	—
		25	25	25	0.8	I	A 80 25 251	—
		30.2	20.15	15.1	0.95	I	A 80 30 150	A 81 30 200
		40.5	13.8	16.1	1.1	I	A 80 40 160	A 81 40 130
		40.2	13.55	25	0.85	I	A 80 40 250	A 81 40 130
		40	40	12.8	1.0	I	A 80 40 130	A 81 40 400
		40.2	40.2	20	1.0	I	A 80 40 200	A 81 40 400
		45.1	30.1	15	1.15	I	A 80 45 150	A 81 45 300
		45.1	30	24.9	1.1	I	A 80 45 250	A 81 45 300
		49.9	13.1	15	1.0	I	A 80 50 150	—
		50.15	50.15	15.1	1.3	I	A 80 50 160	A 81 50 500
		50.1	50.1	25.1	1.3	I	A 80 50 250	A 81 50 500
		50.7	50.7	49.7	1.7	I	A 80 50 500	A 81 50 500
		70	50.4	20	1.4	I	A 80 70 200	A 81 70 500
		70.6	50.4	35	1.4	I	A 80 70 350	A 81 70 500
		90.3	60.3	20	1.6	I	A 80 90 200	—
		100.1	50.2	24.8	1.5	I	A 80 10 250	—
		100	100	40	1.8	I	A 80 10 400	—
	PA 6.6	14	14	11.5	0.7	II	case	
		17.4	15	10.5	0.7	III	A 80 14 118	
		17.4	15	15.3	0.6	II	A 80 17 108	
		18.6	18.6	13.7	0.6	III	A 80 17 158	
		20.8	20.8	12.6	0.8	III	A 80 18 138	
		21.3	13.3	17.7	0.9	III	A 80 20 128	
		22.4	22.4	14	0.8	III	A 80 21 178	
		22.4	22.4	14	0.8	III	A 80 22 148	
		26.4	26.4	35.2	1.1	III	A 80 26 358	
		29	29	19.2	1.0	III	A 80 29 198	
		30.3	30.3	50.3	1.5	III	A 80 30 508	
		32.4	32.4	20	1.0	III	A 80 32 208	
		38.8	38.8	26.6	1.2	II	A 80 39 268	
		38.9	38.9	38.8	1.2	II	A 80 39 398	
		40	10	20.2	1.0	II	A 80 40 208	
		46.2	46.2	40.8	1.1	III	A 80 46 408	
		12.3	12.3	15.3	1.0	III	A 80 12 159	
		21.2	21.2	12.1	1.0	III	A 80 21 129	
	ABS	25.3	25.3	15.2	1.0	III	A 80 25 159	
		38.3	20.4	20.2	1.0	III	A 80 38 209	
		45.5	30.5	15.7	1.2	III	A 80 45 169	
		67.5	35.8	46.3	1.7	III	A 80 67 469	



*1 cases supplied bulk packed