

Protect Fuses from Extreme Conditions

Gasket-sealed, In-line Fuse Holders Seal out Contaminants, Seal in the Power

Superior Seal

Tough cover locks tightly to fuse holder, silicone rubber gasket provides excellent seal

Water and Solvent Resistant

Black nylon housing and PVC insulated leads are highly resistant to attack from water, common solvents and harsh environments

Wide Range of Applications and Demand

Ideal for SUV, ATV, trailer and marine applications where water and contamination of fuse holders are a problem

Handle up to 30 Amps

Five-inch, 12-gauge copper leads come fully assembled, ready for splicing into circuits

Easy, Secure Mounting

Single, built-in mounting hole provides quick and secure installation

Broad Market Coverage with Just Two Holders

New HHU ATM® fuse holder complements the existing HHR ATC® holder for broad and popular blade-type fuse coverage




Gasket-Sealed Inline Blade Fuse Holders



New HHU for ATM® Blade Fuses

Specifications

Volts: Up to 32Vdc	Amps: Up to 30A
Cap & Housing: Nylon	Flammability Rating: UL 94V2
Gasket: Silicone Rubber	Terminals: Tin-plated brass
Lead Wires: (2) 12-gauge; 5", silicone coated and PVC insulated	Available in blister or boxed packaging



	Unit				Shelf Carton				Master Carton					
Part#	UPC Code		Qty	Unit Weight	Bar Code	Qty	Wgt	Cubic Inches	Bar Code	Qty	Cubic Inches	Wgt	Tie	High
HHU	051712	505758	1	0.05	30051712505759	10	0.5	35.25	70051712505757	320	1401.45	17	12	4
BP/HHU	051712	629904	1	0.06	30051712629905	5	0.35	108.74	70051712629903	120	3007.64	8.2	6	3

Cooper Bussmann provides a full line of blade-style fuse holders

Standard Pack	Retail Pack	Max Amps	Gauge	Lead Color	Lead Length	Description
---------------	-------------	----------	-------	------------	-------------	-------------

ATC® Style

HHC	BP/HHC	20	16	black	3.5" each	Does not include cover
HHD	BP/HHD	30	12	yellow	3.5" each	Does not include cover
HHD-C						Cover for HHC and HHD fuse holders
HHD-12						Display contains 12 HHD fuse holders
	BP/HHD-30	30	12	yellow	3.5" each	Same as HHD; also includes ATC-30 fuse
HHF	BP/HHF	20	14	yellow	3.5" each	Splash resistant protective cover
HHG	BP/HHG	30	12	yellow	3.5" each	Splash resistant protective cover
HHR	BP/HHR	20	12	orange	4" each	Locking, sealed-gasket water-resistant cover with mounting hole
	BP/HHS	20			not included	Self-stripping: use #18 to #14 AWG copper wire only (not included)
	BP/HHA	10				Add-a-line converts to 2 circuits; plugs into fuseblock

ATM® Style

HHL	BP/HHL	20	16	black	3.5" each	Splash resistant protective cover
HHM	BP/HHM	30	12	red	3.5" each	Splash resistant protective cover
HHM-B		30	12	red	3.5" each	Does not include cover
HHM-C						Cover only - Fits HHM and HHL fuseholders
NEW HHU	BP/HHU	30	12		4" each	Locking, sealed-gasket water-resistant cover with mounting hole
	BP/HHH	10				Add-a-line converts to 2 circuits; plugs into fuseblock

MAX Style

HHX		60	6	red	5" each	Splash resistant protective cover
HHX-B		60	6			Body only; does not include lead wires
HHX-C		60				Cover only - Fits HHX fuseholder