

| REV. | DESCRIPTION | DATE       |
|------|-------------|------------|
| A    | RELEASE     | 2012.11.12 |

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: flash gold

Contact Material: Brass






Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.


Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C



| NUMBER<br>OF POSITIONS | DIMENSION |      |
|------------------------|-----------|------|
|                        | A         | B    |
| 06                     | 4.0       | 11.2 |
| 08                     | 6.0       | 13.2 |
| 10                     | 8.0       | 15.2 |
| 12                     | 10.0      | 17.2 |
| 14                     | 12.0      | 19.2 |
| 16                     | 14.0      | 21.2 |
| 18                     | 16.0      | 23.2 |
| 20                     | 18.0      | 25.2 |
| 22                     | 20.0      | 27.2 |
| 24                     | 22.0      | 29.2 |
| 26                     | 24.0      | 31.2 |
| 28                     | 26.0      | 33.2 |
| 30                     | 28.0      | 35.2 |
| 34                     | 32.0      | 39.2 |
| 36                     | 34.0      | 41.2 |
| 40                     | 38.0      | 45.2 |
| 44                     | 42.0      | 49.2 |
| 50                     | 48.0      | 55.2 |



| UNLESS TOLERANCE |              | DRAW    |      | CnC Tech,LLC                |  |        |
|------------------|--------------|---------|------|-----------------------------|--|--------|
| GENERAL          | ANGLE        | DESIGN  | BY   |                             |  |        |
| X. ± 0.30        | X.° ± 3.0°   | CHECK   | BY   |                             |  |        |
| .X ± 0.20        | .X° ± 2.0°   | APPROVE | BY   |                             |  |        |
| .XX ± 0.15       | .XX° ± 1.0°  | SCALE   |      | Port NO.<br>3130-XX-0102-00 |  |        |
| .XXX ± 0.10      | .XXX° ± 0.5° |         |      |                             |  |        |
|                  |              | 1:1     | 1/1  | DRAW NO:                    |  | REV: A |
|                  |              | MM      | UNIT |                             |  |        |