

Armored Cable/Flexible Metal Conduit Fittings

T&B Catalog Number:



3132

UPC Number:

78621003132

Status:

Active

Description:

1/2 in. Tite-Bite 90 Degree Insulated Connector, Steel-Electro Zinc Plated, Insulator-Thermoplastic.

Features

By far the easiest and best to install when making sharp bends at the enclosure or equipments.

All the advantages of the straight connector with only one screw to tighten, except in the larger sizes where there are two.

A peep hole on top provides for easy inspection of the ABC bushing.

Narrow design makes it easy to install connectors in adjacent knockouts.

Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

General

Trade Size (inches)	1/2
Material	Steel
Finish	Electro Zinc Plated

Dimension Information

Dimension A (inches)	1 7/8
Dimension B (inches)	2 5/16
Dimension C (inches)	15/16
Knockout Size (inches)	1/2
Cable Opening-Minimum (inches)	0.75
Cable Opening-Maximum (inches)	0.937

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	25
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	21.55 lbs. per 100

Notes

U.L. Listed as a grounding means under NEC 350-5

Certifications

RoHS Compliance	No
-----------------	----

Certifications



File Nbr:
E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com