

1. Material and Finish:

- ### Duplex LC Connector

- Housing: PEI , UL94 V-0,

- Color: **SM Blue/MM Beige/APC SM Green**

- Ferrule Sub Assembly: Zirconia/Metal
- Inner Tubing: PTFE
- Rear Body: Brass, Nickel Plated
- Dust Cap: PC, Color: White

- ③ - Duplex LC Clip: PC, Color: Black



- Crimp Barrel: Brass, Nickel Plated

- Operating Temperature: -40°C to +85°C

2. IP67 rated when covered or fully mated with the appropriate mating connector

- ④ 3. Accept 4.5mm to 8.0mm outside diameter fiber optic cable

- #### 4. RoHS compliant



Description	Part Number
Single Mode (SM)	17-300030
Multi Mode (MM)	17-300040
ⓔ APC Single Mode (APC SM)	17-300110

Directive 2002/95/EC RoHS Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. CONEC CORPORATION OWNERSHIP AND COPYRIGHT © CONEC CORPORATION DO NOT ALTER CAD DRAWING BY HAND	Customer:				Tolerance Unless otherwise specified 0 PLC ±0.30 1 PLC ±0.20 2 PLC ±0.10 3 PLC ±0.05 ANGLES ±1°				Scale: 1.5:1		Dim. in mm	
	Name		Title	Approval Date					Autodesk Inventor		Material: See Notes	
					2008	Date	Name	Title: IP67 Industrial Duplex LC Plug Kit Plastic Version				
					Draw.	Jun. 06	Vincent Ke					
	e	2 x e	Nov/22/10	Vincent ke	Appd.	Jun. 06	J. Chaudry					
								Drawing No.: 17K1A003 Part No.: SEE P/N ABOVE				
	d	1 x d	Nov/03/10	Vincent Ke	Norm							
	c	1 x c	Jul/19/10	Vincent Ke	D-old							
								DIN A3 Sheet 1/1				
	b	1 x b	May/28/09	Vincent Ke								
a	original											
Rev.	Changes	Date	Name									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-300110](#)