




Standard: Gold flash
30 option: 30u" gold
50 option: 50u" gold
to comply with FCC
requirements under #47
C.F.R. Part 68,
Subpart F

Durability Rating:
500 mating Cycles Min.

Shielded types offer 20dB shielding from 30MHz to 300MHz

Dimensions					mm			
Part Number	A	B	C	D	Gold Plating Option	# of Ports	Style of Board Peg	
GSG-NS2-288-368	31.12	25.40	30.87	3.68	Standard	2	snap-in	
GSG-NS2-288-457	31.12	25.40	30.87	4.57				
GSG-NS2-288-368-50	31.12	25.40	30.87	3.68	50			
GSG-NS2-288-457-50	31.12	25.40	30.87	4.57				
GSG-NS2-488-368	59.03	53.34	58.81	3.68	Standard	4		
GSG-NS2-488-457	59.03	53.34	58.81	4.57				
GSG-NS2-488-368-50	59.03	53.34	58.81	3.68	50			
GSG-NS2-488-457-50	59.03	53.34	58.81	4.57				
GSG-NS2-588-368	73.03	67.31	72.78	3.68	Standard	5		
GSG-NS2-588-457	73.03	67.31	72.78	4.57				
GSG-NS2-588-368-50	73.03	67.31	72.78	3.68	50			
GSG-NS2-588-457-50	73.03	67.31	72.78	4.57				
GSG-NS2-688-368	87.00	81.28	86.75	3.68	Standard	6		
GSG-NS2-688-457	87.00	81.28	86.75	4.57				
GSG-NS2-688-368-50	87.00	81.28	86.75	3.68	50			
GSG-NS2-688-457-50	87.00	81.28	86.75	4.57				
GSG-NS2-888-368	114.94	109.22	114.69	3.68	Standard	8		
GSG-NS2-888-457	114.94	109.22	114.69	4.57				
GSG-NS2-888-368-50	114.94	109.22	114.69	3.68	50			
GSG-NS2-888-457-50	114.94	109.22	114.69	4.57				



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[GSG-NS2-288-368](#) [GSG-NS2-488-368](#)