



Miniature Fuses

Ceramic Tube

F

 Size
6.3 x 32 mm

 Rated Voltage
500 V
Fast Acting

 Standard
Not Standardized

Rated Current [A]	Part No.	Voltage Drop [mV]	Pre-arcing I ² t _s -value [A ² s]	Rated Breaking Capacity [kA]	Power Dissipation [W]	ULrec.	Weight [kg/100]	Pack
0.160	189 020.0.160	7 000	0.0015	150 *	2.5	✓	0.24	100
0.200	189 020.0.200	6 500	0.0035	150 *	2.9	✓	0.24	100
0.250	189 020.0.250	6 000	0.0085	150 *	3.4	✓	0.24	100
0.315	189 020.0.315	1 000	0.025	150 *	0.9	✓	0.24	100
0.400	189 020.0.400	900	0.045	150 *	1.0	✓	0.24	100
0.500	189 020.0.500	800	0.09	150 *	1.1	✓	0.24	100
0.630	189 020.0.630	700	0.15	150 *	1.3	✓	0.24	100
0.800	189 020.0.800	600	0.3	150 *	1.4	✓	0.24	100
1	189 020.1	400	0.4	50 **	1.2	✓	0.24	100
1.25	189 020.1.25	300	0.8	50 **	1.3	✓	0.24	100
1.6	189 020.1.6	300	1.5	50 **	1.4	✓	0.24	100
2	189 020.2	280	2.5	50 **	1.6	✓	0.24	100
2.5	189 020.2.5	260	5	50 **	1.8	✓	0.24	100
3.15	189 020.3.15	240	9	50 **	2.3	✓	0.24	100
4	189 020.4	220	18	50 **	2.6	✓	0.24	100
5	189 020.5	190	40	50 **	2.9	✓	0.24	100
6.3	189 020.6.3	170	80	50 **	3.2	✓	0.24	100
8 ¹	189 020.8	160	150	150 *	3.7		0.24	100
10 ¹	189 020.10	150	240	150 *	4.0		0.24	100
12.5 ¹	189 020.12.5	140	500	150 *	5.5		0.24	100
16 ¹	189 020.16	130	920	150 *	6.5		0.24	100

 Size
6.3 x 32 mm

 Rated Voltage
440 V
Fast Acting

 Standard
Not Standardized

Rated Current [A]	Part No.	Voltage Drop [mV]	Pre-arcing I ² t _s -value [A ² s]	Rated Breaking Capacity [A]	Power Dissipation [W]	ULrec.	Weight [kg/100]	Pack
20 ¹	189 020.20	120	1 500	1500	8.4		0.24	100
25 ¹	189 020.25	110	3 100	1500	11		0.24	100

¹ Consideration should be given to heat dissipation.

* @ 500 V AC

** @ 500 V AC and 20 kA @ 500 V DC approved