

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

The technical drawing shows a 2x10 label holder with the following dimensions:

- Overall width: 2.950 [74.93]
- Inner width: 2.750 [69.85]
- Label height: 1.250 [31.75] TYP. REPEAT
- Label height: 1.375 [34.92] TYP. REPEAT

PART NO.	MATERIAL	MARKER SIZE inches [mm]	COLOR	LABELS PER ROW	LABELS PER PKG.
C275X125YPT	GMY4-HTW	2.000 [50.80] X 1.000 [25.40]	WHITE	1	2500
C275X125YOT			TIA BLACK		
C275X125AAT	GMY4STE		SILVER		
C275X125YMT	GMY4-S		SILVER		
C275X125YJT	GMY4-W		WHITE		

NOTES:
 1. MILLIMETER ARE IN [].
 2. SEE MFG. DRAWING NO. A61387.

									CAD FILENAME/LAYERS 1004720Y_C10573_C275X125xxT_02.prt	
									PANDUIT CORP. TINLEY PARK, ILLINOIS	
									CUSTOMER DRAWING OPTIMUM C275X125**T THERMAL TRANSFER PRINTABLE LABELS	
									UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (XXX) ± .010 (.XX) ± .015 ANGLES ±	
2	10/30/07	RVU		GMY4-S WAS GMY4-HTS.	5194	R			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
1	5/17/07	RVU		ADDED NEW P/N, C275X125YMT AND C275X125YJT.	5003	R			DRAWN BY RVU	
0	1-30-06	RVU		DRAWING RELEASE.	4924	R			DATE 2-1-05	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	CHK'D	
									MAT'L; SEE TABLE	
									SCALE NTS	
									DRAWING NO. C10573	
									DWG A SIZE	