


NOTES

1. PLEASE SEE SHEET 2 FOR CURRENTLY CONFIGURED PART NUMBERS.
FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT
THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED.
2. EARTH POSITION SHOWN, H12
3. FOR PACKAGING SEE PACKAGING SPEC PK-121023-C19
4. PRODUCT SPEC: SEE PS-121201-001
5. PART NO 1210230465 SHOWN FOR ILLUSTRATION PURPOSES ONLY

LAST INSPECTION NUMBER 2



ITEM	DESCRIPTION
1	SCREW
2	COVER ASSEMBLY
3	INSERT ASSEMBLY
4	GASKET

C19307N22**

SERIES

C19= INTERNAL THREAD FORM C MICRO

POLES

2= 2 POLE, 3= 3 POLE

THREAD SIZE

07= PG7, M2=M12x1.5

MATERIAL AND HOUSING COLOUR

G= PA6 GRAY, N= PA6 BLACK, W= PA6 BLACK V0, T= TRANSPARENT

GROUND POSITION

0= UNMOUNTED, 2= H12, 3= H3, 6= H6, 9= H9

SCREW AND GASKET

1= NBR PROFILE GASKET & SCREW

2= NBR FLAT GASKET & SCREW

3= WHITE SILICON PROFILE GASKET & SCREW

4= WHITE SILICON FLAT GASKET & SCREW

6= NBR FLAT GASKET, NO SCREW

A= NBR PROFILE GASKET & SCREW +2mm

B= NBR FLAT GASKET & SCREW +2mm

C= WHITE SILICON PROFILE GASKET & SCREW +2mm

D= WHITE SILICON FLAT GASKET & SCREW +2mm

NON STANDARD COMPONENTS

14= SINGLE PACKED IN NEUTRAL BAG

5N= SINGLE PACKED

6X= WITHOUT RING NUT OR CABLE FIXING NUT

P7= IP67 COMPLIANT

SA= UL LISTED

0217= THREE BAGS OF 100 PER BOX

ADDED PART NUMBERS		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: IPG2014-1003		▽=0		mm		MM ONLY		2:1		METRIC		THIRD ANGLE PROJECTION	
DRAWN: KNOXMOYLE		▽=0		INCH		DRAWN BY		DATE		TITLE		INTERNAL THREAD	
2013/12/02						DSHEA		2011/05/18				C19 SERIES	
CHKD: DSHEA						CHECKED BY		DATE					
2013/12/02						DMAHER		2011/05/27					
APPR: STGRIFFIN						APPROVED BY		DATE					
2014/01/08						EFOLAN		2011/06/08					
						MATERIAL NO.		DOCUMENT NO.					
						SEE SHEET 2		SD-121023-005					
						SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX					
						A2		INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

