

Knopfskalen

Knopf Aluminium eloxiert. Zeiger Federbronze vernickelt. Ringmutter M 10 x 0,75. Anzeigebereich 0 bis 10 auf 270°.



Ø d	Ø D	Art.-Nr.
6	10,2	148.621

Potentiometer-Befestigung mit Skaleneinteilung. Aluminium eloxiert.



Ø d	Ø D	Anzeigebereich Scale Subdivision	Art.-Nr.
M 7 x 0,75	4	360° (0-10)	145.41
M 10 x 0,75	6	360° (0-10)	145.61
M 7 x 0,75	4	270° (0-10)	6145.2234
M 10 x 0,75	6	270° (0-10)	6145.2236

Kleinskalen mit Feststellvorrichtung

Miniaturausführung einschließlich Befestigungsmutter für Potentiometerbefestigung. Bei diesen Kleinskalen handelt es sich um montagefertig komplett gelieferte Skalenaggregate. Mit einer Feststellschraube kann jede gewünschte Skaleneinteilung fest arretiert werden. Grundplatte Thermoplast. Skala Aluminium eloxiert.




Ø d	Ø D	Anzeigebereich Scale Subdivision	Art.-Nr.
4	7,1	270°	6156.2234




Ø d	Ø D	Anzeigebereich Scale Subdivision	Art.-Nr.
4	10,2	270°	149.224
6	10,2	270°	149.22

Knob-Type Scales

Knob: aluminum anodized. Pointer: phosphorus bronze, nickel-plated. Ring nut: M 10 x 0.75. Scale Subdivision 0 to 10 at 270°.



Potentiometer mount with scale setting. Aluminium anodized.



Miniature Scales with Arresting Device

Miniature type with mounting nut for potentiometer. These miniature scales are scale units that come completely and ready for assembly. With a locking screw, any desired scale setting can be firmly arrested. Base plate: Thermoplastic. Scale: aluminum anodized.

