



586-4606-801

- Designed for LED Reading Light Applications
- Bayonet Base
- 20 degree circular beam pattern
- 55 mAmps @ 24 VDC
- 70 lux @ 1 meter, 350 lux @ 0.5 meter




13001CB - 12 Volt , 13003CB - 24 Volt (Preliminary Information)

- 2.5" x 1" Mini Design
- .180 bullet wire termination
- Potted construction
- 45 degree x 10 degree beam pattern
- 30 mAmps @ 12 VDC, 15 mAmps @ 24 VDC
- 8 lux @ 1 meter, 30 lux @ 0.5 meter





17081CB - 12 Volt, 17083CB - 24 Volt

- Lens includes optics to disperse light
- 2.5" Lens diameter w/ Black Flange
- Weather Pak connector wire termination
- Welded Design
- 45 degree x 10 degree beam pattern
- 175 mAmps @ 12 VDC, 80 mAmps @ 24 VDC
- 23 lux @ 1 meter, 120 lux @ 0.5 meter



17081CB802 - 12 Volt , 17083CB803 - 24 Volt

- Clear Lens for spot lighting
- 2.5" Lens diameter w/ Black Flange
- Weather Pak connector wire termination
- Welded Design
- 20 degree circular beam pattern
- 175 mAmps @ 12 VDC, 80 mAmps @ 24 VDC
- 98 lux @ 1 meter, 450 lux @ 0.5 meter



Note: Contact your Dialight sales representative for custom wire lengths and custom terminations.

Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA


Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com

●●●●●●●●●●
a Roxboro Group Company

MDTBWLXP001_C


46121CB - 14 Volt, 46123CB - 24 Volt

- 4" Round Back up Lamp
- Weather Pak connector wire termination
- Potted construction
- Includes lens hard coating
- 180 mAmps @ 14 VDC, 120 mAmps @ 24 VDC




46001CB801 - 14 Volt, 46003CB811 - 24 Volt

- 4" Round Lamp with dispersing optics
- Weather Pak connector wire termination
- Potted construction
- 45 degree x 10 degree beam pattern
- 360 mAmps @ 14 VDC, 110 mAmps @ 24 VDC
- 260 lux @ 1 meter, 1120 lux @ 0.5 meter




47001CB • 12 Volt High Intensity

- Low intensity version also available
- 4" Round Lamp with a clear lens
- Potted construction
- 12 inch wire termination




71121CB - 14 Volt, 71123CB - 24 Volt

- 7" Round Back-up Lamp
- Weather Pak connector wire termination
- Potted construction
- Includes lens hard coating
- 360 mAmps @ 14 VDC, 325 mAmps @ 24 VDC



87001CB - 12 Volt, 87003CB - 28 Volt

- 18" x 0.75" with diffused Lens
- EDAC connector wire termination
- Potted Construction
- Wide angle uniform beam
- 20 degree circular beam pattern
- 270 mAmps @ 12 VDC, 170 mAmps @ 28 VDC
- 8 lux @ 1 meter, 38 lux @ 0.5 meter



Note: Contact your Dialight sales representative for custom wire lengths and custom terminations.

Dialight Corporation

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com

●●●●●●●●●●
a Roxboro Group Company