

USB / FireWire ® - USB 1.1 Cable (iMac Blue)

MODEL NUMBER: **U002-006-IB-R**

Description

Tripp Lite's 6-ft. USB A/B device cable is designed to connect a USB device to the USB port on a computer or USB hub. This high quality cable delivers the performance and reliability you expect from a USB cable. The cable features gold plated copper contacts for superior conductivity. It is manufactured with molded connectors which include integral strain relief to ensure durability. Double shielding provides maximum EMI/RFI protection. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil feature twisted 28/20 AWG data lines
- Gold plated contacts provide superior conductivity
- Molded connectors which include integral strain relief to ensure durability
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Highlights

- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/20 AWG data lines
- Gold plated connectors provide superior conductivity for low and high speed devices (1.5 to 12 Mbps.)
- Retail packaging

Package Includes

- 6-ft. USB AB Cable USB-A to USB-B, Blue

Specifications

General Info	
Product Group	USB & FIREWIRE CABLES
INPUT	
Cable Length (ft.)	6
UPC ASSIGNMENT	
Unit Carton UPC#	037332014634
CONNECTIONS	
Connector A	USB A (MALE)
Connector B	USB B (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.