





D-Subminiature Connectors

152-3609, 152-3615, 152-3625



D-Subminiature Connectors



Dimensions: mm (IN.)

SPECIFICATIONS

Insulation resistance:	5,000MΩ min. @ 500VDC
Contact resistance:	20mΩ max. @ 100mADC
Current rating:	1A
Withstand voltage:	1,000VAC for 1 minute
Operating temperature:	-55°C ~ + 105°C
Contact:	Brass
Housing:	PBT & 30% glass fiber
Type:	Filtered, right angle, female
Plating:	Gold plated

Mouser Stock No.	No. of Contacts	Dimensions		
		A	B	C
152-3609	9	.64	.98	1.2
152-3615	15	.97	1.3	1.5
152-3625	25	1.5	1.8	2.1

Date Last Revised: 10-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300259

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[152-3625](#) [152-3615](#) [152-3609](#)