



ANXB4502N



Product Description

B4502N 450-470 MHz, 2.4 DBD GAIN, NO GROUND PLANE, MOBILE, N/A CONNECTOR

Technical Specifications

alpha frequency	UHF
cable	N/A
mount type	3/4" hole
maximum power (W)	200W
connector	N/A
gain	2.4 dBd
frequency (bandwidth)	450-470 MHz
VSWR	<2:1
wavelength	1/2

whip length	10-5/16"
whip material	stainless steel
Height	10.4"
Weight	2.05 LB
Warranty	1 year
Shipping *	Parcel Freight