

UT58E
[Enlarge](#)


Registered Design No.: 0211977.6M001

[Download Manual](#)
Modern Digital Multimeters**SPECIFICATIONS**

Basic Functions	Range	Best Accuracy
DC Voltage	200mV/2V/20V/200V/1000V	$\pm (0.05\%+3)$
AC Voltage	2V/20V/200V/1000V	$\pm (0.5\%+10)$
DC Current	2mA/200mA/20A	$\pm (0.5\%+5)$
AC Current	20mA/200mA/20A	$\pm (0.8\%+10)$
Resistance	200 Ω /2k Ω /20k Ω /2M Ω /200M Ω	$\pm (0.5\%+10)$
Capacitance	2nF/20nF/2 μ F/20 μ F	$\pm (3\%+40)$
Temperature($^{\circ}$ C)	-40 $^{\circ}$ C ~ 1000 $^{\circ}$ C	$\pm (1\%+30)$
Frequency	20kHz	$\pm (1.5\%+5)$
Special Functions		
Diode		✓
Continuity Buzzer		✓
Transistor		✓
Data Hold		✓
Full Icon Display		✓
Sleep Mode		✓
Low Battery Display		✓
Input Impedance for DC Voltage Measurement	Around 10M Ω	✓
Max Display	19999	✓

GENERAL CHARACTERISTICS

Power	9V Battery (6F22)
LCD Size	60 x 54mm
Product Colour	Grey Holster - Red
Product Net Weight	350g (including holster)
Product Size	179 x 88 x 39mm
Standard Accessories	Test Lead, Battery, English Manual, Point Contact Temperature Probe, Test Clip, Multi-Purpose Socket, Holster
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	40pcs
Standard Carton Measurement	598 x 418 x 340mm (0.085 CBM Per Standard Carton)
Standard Carton Gross Weight	27kg

Specifications and other information are subject to change without further notice.

[Back to main menu](#)