


3mm

LED CBI® Circuit Board Indicator
In-line, 3 Leaded Bi-Color

NEW

Dialight

551-3508-801



PART NO.

551-3508-801

COLOR

Red/Green

Dimensions in mm [inches]

Features

- Common Cathode simplifies design, and provides amber as a third color
- Locating pin provides stability during soldering
- Multiple CBIs form horizontal LED arrays on 4.2mm (0.1650") center-lines
- High Contrast, UL 94 V-0 rated, black housing
- Oxygen index: 31.5%
- Polymer content: PBT, 1.055 g
- Housing stand-offs facilitate PCB cleaning
- Solderability per MIL-STD-202F, method 208F
- LEDs are safe for direct viewing per IEC 825-1, EN-60825-1

Tolerance note: As noted, otherwise:

- LED Protrusion: ±0.04 mm [±0.016]
- CBI Housing: ±0.02mm[±0.008]

Typical Operating Characteristics ($T_A=25^\circ\text{C}$)

See page 4-70 and 4-71 for Reference Only. LED Drive Circuit Examples. See page 4-72 for Pin Out

| Part Number | Color | Peak Wavelength nm | I _V mcd | V _F Volts | Test Current (mA) | LED Data sheet | Page # |
|--------------|-----------|--------------------|--------------------|----------------------|-------------------|----------------|--------|
| 551-3508-801 | Red/Green | 630/560 | 4/4 | 2/2.1 | 20 | 3TF-9484 | 4-69 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

551-3508-801