

6 outlet, 6-ft cord, 360 joules Protect It! Surge Suppressor

MODEL NUMBER: **TLP6B**



Highlights

- 6 outlet / 6-ft cord
- 360 joule rating
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for any desktop, network or home computing application requiring AC line protection

Package Includes

- TLP6B surge suppressor

Description

Tripp Lite's TLP6B offers economical AC surge suppression for protection of workstations, desktop PC's, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP6B offers 6 total outlets, 6 foot cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 360 joules shields equipment from surges and line noise. Attractive black suppressor housing with keyhole mounting tabs offer convenient protection of desktop computer equipment and accessories. \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P / Output: 6 NEMA5-15R / 6-ft AC line cord

ELECTRICAL: 120V AC, 60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer spaced outlet

SUPPRESSION: AC: 150V RMA Clamping / 360 joules/ 500V UL1449 3rd Edition

Features

- 6 outlets
- 6-ft cord
- Surge suppression rating: 360 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Green "Protected" LED
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate 1 large transformer plug without covering remaining outlets, 3 total transformers
- Keyhole support for wall mounting
- Lighted power switch
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

General Info	
Product Group	SURGE PROTECTORS
OVERVIEW	
Intended Application	Home / Office
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1875
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Outlet Quantity / Type	6 NEMA 5-15R
Number of Outlets	6
Transformer Accommodation	Supports 1 large transformer plug accessory without blocking remaining outlets, accepts up to 3 transformers total
Outlet Orientation	Single row of 6 outlets
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	24000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	360
AC Suppression Response Time	< 1 ns
Protection Modes	L-N
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	500v

EMI / RFI Filtering	up to 20dB
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.21 x 3.77 x 1.10
Shipping Dimensions (hwd / cm)	23.39 x 9.58 x 2.79
Shipping Weight (lbs.)	.86
Shipping Weight (kg)	0.39
Unit Dimensions (hwd / in.)	11.25 x 3.77 x 1.10
Unit Dimensions (hwd / cm)	28.58 x 9.58 x 2.79
Unit Weight (lbs.)	.81
Unit Weight (kg)	0.37
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Black
Receptacle Color	Black
Color (AC Line Cord)	Black
Style	Strip
CERTIFICATIONS	
Additional International Approvals	RoHS
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance