

PM-15 Series - 15W Single Output Encapsulated Medical PSU

[Home](#) > [Products](#) > [Medical](#) > 15W Single Output Encapsulated Medical PSU

Features

Standards

- Universal AC input/full range
- Ultra low profile
- Isolation class II
- No load power consumption <0.5W
- Short circuit, OLP & OVP
- UL60601-1 & TUV EN60601-1 medical safety approved
- Cooling by free air convection
- Fixed switching frequency at 67KHz



Applications

- Non-patient contact medical
- General electronics
- IT equipment
- Industrial

Case Details

75 x 53 x 22.7mm


Specification

Input Voltage	85 ~ 264VAC 120 ~ 370VDC
Input Frequency	47 ~ 440Hz
AC Current	0.35A/115VAC 0.2A/230VAC
Inrush Current	30A/115VAC 50A/230VAC typically, cold start
Setup, Rise Time	1000ms, 20ms/230VAC 1000ms, 20ms/115VAC at full load
Holdup Time	100ms/230VAC 20ms/115VAC typically at full load
Overload Protection	Above 105% rated output power Hiccup mode, recovers automatically after fault condition is removed
Over Voltage Protection	Protection type Shut off
Working Temperature	-20°C to +70°C (Refer to output load derating curve)
Working Humidity	20 ~ 90% RH non-condensing
Storage Temperature, Humidity	-40°C to +85°C, 10 to 95% RH
Temp Coefficient	±0.03%/°C (0 ~ 50°C)
Vibration	10 ~ 500Hz, 2G 10min./1cycle, Period for 60min.each along X, Y, Z axes
Safety Standards	UL60601-1,TUV EN60601-1 Approved
Withstand Voltage	I/P-O/P:4KVAC
Isolation Resistance	I/P-O/P:100M Ohms/500VDC
EMC	Compliance to EN55011(CISPR11), EN55022 (CISPR22) Class B, EN61000-3-2,-3 EN61000-4-2,3,4,5,6,8,11; ENV50204, EN55024, EN60601-1-2, EN61204-3 Medical level, criteria A.
MTBF	499.7Khrs min. MIL-HDBK-217F (25°C)
Dimensions	75 x 53 x 22.7mm


Items

PM-15 Series Output Data


Part Code	Voltage	Rated Current	Current Range	Rated Power	R&N
PM-15-3.3	3.3V	3.5A	0 ~ 3.5A	11.55W	80mV
PM-15-5	5V	3A	0 ~ 3A	15W	80mV
PM-15-12	12V	1.25A	0 ~ 1.25A	15W	150mV
PM-15-15	15V	1A	0 ~ 1A	15W	150mV
PM-15-24	24V	0.63A	0 ~ 0.63A	15.12W	240mV
.					
Part Code	Tol.	Line Reg.	Load Reg.	Eff.	OVP
PM-15-3.3	±3.0%	±1.0%	±1.0%	73%	3.8 ~ 4.95V
PM-15-5	±2.0%	±1.0%	±1.0%	76%	5.75 ~ 6.75V
PM-15-12	±2.0%	±0.5%	±0.5%	78%	13.8 ~ 16.2V
PM-15-15	±2.0%	±0.5%	±0.5%	79%	17.25 ~ 20.25V
PM-15-24	±2.0%	±0.5%	±0.5%	81%	27.6 ~ 32.4V



Output Derating



Output Derating VS Input Voltage



Related Documents

- PM-15 Series Mechanical Diagram (429KB)
- PM-15 Series Block Diagram (257KB)
- PM-15 Series CE Declaration (22KB)
- PM-15 Series TUV Certificate (76KB)
- PM-15 Series RoHS Declaration (89KB)
- PM-15 Series CB Certificate (163KB)
- PM-15 Series cUL Certificate (123KB)
- PM-15 Series UL Certificate (122KB)