



## Rigid/IMC Conduit Fittings

### T&B Catalog Number:

375

**UPC Number:**

78621000375

**Status:**

Active

**Description:**

2 in. Hub Connector, Malleable Iron-Electro Zinc Plated, Nylon Insulated.  
For use with Rigid/IMC Conduit.

### Features

|  |                                                                                                                                                                                         |
|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | Rugged steel/malleable iron construction                                                                                                                                                |
|  | Tapered internal threads for water-tight/dust-tight union                                                                                                                               |
|  | Threads relieved to prevent bottoming of conduit, ensuring sound assembly                                                                                                               |
|  | Recessed sealing ring at box end; sealing ring cap-tivated                                                                                                                              |
|  | Hardened steel/malleable iron/copper-free aluminum locknuts designed to provide high quality ground continuity; extended reach of locknut permits clamping on thin boxes and enclosures |
|  | Insulated throat, insulates conductors, prevents abrasion and thinning of conductor insulation, reduces wire pull effort                                                                |

### Application

|  |                                                                                                                                                                                                                                  |
|--|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | To connect threaded metal conduit (ferrous rigid/non-ferrous rigid/PVC coated/or intermediate metal) to a threadless opening in a box or enclosure in outdoor or indoor location exposed to continuous or intermittent moisture. |
|  | To positively bond conduit to box or enclosure.                                                                                                                                                                                  |
|  | Suitable for hazardous locations use in Class I, Division 2; Class II, Division 1&2; Class III, Division 1 & 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a).                                                                        |
|  | Suitable for hazardous locations use in Class II, Groups E, F, G & Class III locations per CEC 18-202; 18-252; 18-302; 18-352.                                                                                                   |
|  | When used with neoprene O-ring, provides water-tight threaded hub on enclosures                                                                                                                                                  |
|  | UL Listed 105 degree C                                                                                                                                                                                                           |

### General

|                     |                     |
|---------------------|---------------------|
| Trade Size (inches) | 2                   |
| Material            | Malleable Iron      |
| Finish              | Electro Zinc Plated |

### Dimension Information

|                      |       |
|----------------------|-------|
| Dimension A (inches) | 3 5/8 |
| Dimension B (inches) | 1 5/8 |
| Dimension C (inches) | 1     |

### Specifications

|         |                      |
|---------|----------------------|
| 3dmodel | Available on Website |
|---------|----------------------|

### Packaging

|                  |   |
|------------------|---|
| T&B Inner Pack   | 1 |
| Package in Units | 5 |

|                    |                  |
|--------------------|------------------|
| T&B Sold in UOM    | Each             |
| T&B Weight Per UOM | 112 lbs. per 100 |

## Application Support

|               |                      |
|---------------|----------------------|
| Spacing Chart | Available on Website |
|---------------|----------------------|

## Notes

Available with DURA-PLATE Finish

## Certifications

|                 |     |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

## Certifications



File Nbr:  
E 23018

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)