




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



RECOMMENDED PANEL OPENING
(MAX PANEL THICKNESS: 0.06")





APPLICATION NOTES:
ALL PINS WIRED STRAIGHT THROUGH


LABELING:
PANTONE 2945 BLUE. "L-COM" FONT MyriaMM ITALIC.
"GENDER CHANGER" FONT ARIAL BOLD, TEXT HEIGHTS: .085"
TEXT COLOR; WHITE.

Component Specifications	
Material	
Shell	Steel
Contacts/Terminals	Copper Alloy
Hardware	Brass
Insulator	PBT Fiber Reinforced (UL 94V-0 Rated)
Finish	
Shell	Tin/Nickel Plated
Contacts/Terminals	Gold Flash Plated: 1 - 1.5µ inches
Hardware	Nickel Plated
Electrical	
Current Rating	3 AMP
Insulation Resistance	1000 MΩ Min @ 500 VDC
Dielectric Withstanding Voltage	1000 VAC (for One minute)
Environmental	
Operational Temperature Range	-55°C to +105°C


CS-131




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
D	ECN #1690 - CHG'D COMPONENT SPECIFICATION TABLE	01/06/04	B.MAZERKA
E	REVISED/ADDED HARDWARE DETAIL (ECN #1284)	01/06/03	MCCORMICK
F	REVISED/UPDATED ELECTRICAL SPECS	02/23/03	MCCORMICK
G	ECN# 2688, REVISED SHEET TOLERANCE	01/17/07	MCCORMICK



JACKSCREW & HEX STANDOFF
SPECIFICATION



OUTLINE DRAWING



APPROVALS		DATE
DRAWN BY	D.PARIAM	11/12/2001
CHECKED BY	T.CLARK	11/12/2001
APPROVED BY	R.CARRICK	11/13/2001

L-com COMMUNICATIONS PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY		D-SUBMINIATURE	
PRODUCT DESCRIPTION GENDER CHANGER, DB9 FEMALE/FEMALE			
SIZE	PSCM NO.	DWG. NO.	REV.
B	43321	DGB9F-OD1	G

SCALE: 2:1 CAD FILE: DGB9F-OD1.DDORW SHEET 1 OF 1