






Recommended PCB Layout
(Top View)

Materials and Finish

Housing Material-
PBT Thermoplastic
UL 94V-0 Rated
Color: Grey

Contact Material-
Phosphor Bronze

Contact Plating Options-
Standard- 0.000015" gold on entire
contact, 0.0001" nickel
underplating

-50 Option: 0.000050" gold on entire
contact to comply with FCC
requirements under No. 47 C.F.R
Part 68, Subpart F,
0.0001" nickel underplating

Electrical Characteristics

Insulation Resistance-
500 Megohms Min.

Dielectric Withstanding Voltage-
1000V rms, 60Hz

Contact Resistance-
20 milliohms Max.

Current Rating-
1.5 Amps

Part Number	Contact Area Plating Finish
GL-N-64M	15u" Gold (standard)
GL-N-64M-50	50u" Gold (-50 option)



Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise

REVISION	DATE	DESCRIPTION	DRAWN BY	REV CHECK BY	UNITS
A2	6/21/02	ECD #02-005	J. Kring	T. Gokcek	mm
A3	8/12/02	ECD #02-013	REVISED BY	REV CHECK DATE	DATE
B1	9/16/03	ECD #03-031	H. MA	9/18/03	12/02/98

GL-N-64M

Mod. Jack, Rt Ang PCB Mount

6 position, 4 contacts, M Body



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[GL-N-64M-BLK](#) [GL-N-64M](#) [GL-N-64M-50](#)