

Technical drawing of a PANDUIT connector. The drawing shows two views of the connector. The top view is labeled "PANDUIT" and shows a central circular feature with two vertical slots. The bottom view is also labeled "PANDUIT" and shows a similar central feature with two horizontal slots. Dimensions are indicated: a vertical dimension of 1.13 (28.7) and a horizontal dimension of 1.13 (28.7). A callout line points to the bottom view with the text "COUNT FOR".

- COUNTERSUNK HOLE
FOR OPTIONAL #6 (M3)
SCREW OR 1/8" RIVET.

PANDUIT PART NUMBER*	WEIGHT lbs/100 pcs (g)/100 pcs	USE WITH THESE CABLE TIE CROSS-SECTIONS
ABMS-A	0.42 (189)	M, I, S

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS FOR PACKAGE SIZE.
- 2) MOUNTS PROVIDED IN STRIPS OF TWO FOR EASY REMOVAL OF PROTECTIVE LINER.
- 3) MOUNTS WILL BE ORIENTED IN LINE WITH, OR 90° FROM EACH OTHER AS ILLUSTRATED ABOVE.

ADHESIVE BACKING:
PRESSURE SENSITIVE FOAM TAPE
0.04 (1.0) THICK WITH PROTECTIVE
LINER. MOUNT IS DESIGNED TO
SUPPORT 0.6 lb. (272g.) MAX. WEIGHT
ON A CLEAN, DRY, SMOOTH, GREASE-FREE
SURFACE.

GAD FILENAME/LAYERS

PANDUIT

ABMS-A
ADHESIVE BACKED MOUNT

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (1.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

CCS

MAT'L 8

ESCNLRE

NONE

DATE _____

2-11-68

NYLON 6/6

OFFICIAL USE ONLY

GB0239GE

A

I	2/7/05	JAD	N/A	.205 WAS .200 CORRECTION: .17 WAS .250	GB0239GE	I				
R	2-11-08	CGSM		INITIAL RELEASE	GB0239GE	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			