



DIN 338/BS 328

Point angle 135° split point

Surface treatment Bronze

Application For steels of high tensile strength, stainless and heat resistant steels

Angle, drill point	135 °
Diameter, External	4.00 mm
Length, effective	43 mm
Length, overall	75 mm
Material	HSCo
RoHS Compliant	NA