## Terminal boxes KL






**Material:**
Stainless steel 1.4301
Enclosure: 1.25 mm
Cover: 1.25 mm

**Surface finish:**
Case and cover:
Brushed, grain 180

**Protection category:**
IP 66 to EN 60 529/10.91, complies with NEMA 4x.

**Supply includes:**
Enclosure, cover with all-round foamed-in PU seal and cover screws, including plastic bushes.

**Approvals,**
see page 23.

**Detailed drawing,**
see page 1119.

| **Width** (B1) in mm | Packs of | 150 | 300 | 200 | 300 | 400 | 300 | Page |
|---|---|---|---|---|---|---|---|---|
| **Height** (H1) in mm | | 150 | 150 | 200 | 200 | 200 | 300 | |
| **Depth** (T1) in mm | | 80 | 80 | 80 | 80 | 120 | 120 | |
| **Model No. KL** | 1 | **1521.010** | **1522.010** | **1523.010** | **1524.010** | **1525.010** | **1526.010** | |
| Weight (kg) | | 1.3 | 1.8 | 1.8 | 2.4 | 3.6 | 3.9 | |
| Cover screws | | 4 | 4 | 4 | 4 | 4 | 4 | |
| **Accessories** | | | | | | | | |
| Mounting plate | 1 | 1560.700 | 1561.700 | 1562.700 | 1563.700 | 1564.700 | 1567.700 | 909 |
| Wall mounting bracket | 4 | 1594.000 | 1594.000 | 1594.000 | 1594.000 | 1594.000 | 1594.000 | 905 |
| Wall angle | 1 | 2583.000 | 2583.000 | 2583.000 | 2583.000 | 2583.000 | 2583.000 | 906 |
| Pole clamp | 1 | 2584.000 | 2584.000 | 2584.000 | 2584.000 | 2584.000 | 2584.000 | 906 |
| Support rails TS 35/7.5 | 10 | 2314.000 | 2316.000 | 2315.000 | 2316.000 | 2317.000 | 2316.000 | 927 |

**To order terminal boxes in 1.4404 (AISI 316L), please add extension .510 the the Model No. Delivery times available on request.**



**Wall mounting bracket**
for secure attachment to the wall.
Model No. see page 905.

**Housing coupling**
for attaching the 120 mm deep KL to the support arm system.
Model No. see page 278.

**Accessories** Page 832 **Terminal boxes KL sheet steel** Page 107 **Terminal boxes KL Ex-proof** Page 287