

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190160039

Status:

Active

Description:


Krimptite™ Quick Disconnect, Female, for 14-16 (2.00-1.30) Wire, Box, Tab 4.75mm (.187") x 0.51mm (.020")

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Quick Disconnects
Series	19016
Comments	Butted Seam
Product Name	Krimptite™
Type	Quick Disconnect
Physical	
Barrel Type	Closed
Gender	Female
Glow-Wire Compliant	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Orientation	Straight
Packaging Type	Bag
Polarized to Mating Part	No
Tab Thickness	0.51mm (.020")
Tab Width	4.75mm (.187")
Temperature Range - Operating	Per Wire Specification
Wire Size AWG	14
Wire Size AWG	16
Wire Size mm²	1.30 - 2.00
Electrical	
CSA	LR18689
UL	E79133
Voltage - Maximum	Per Wire Specification
Material Info	
Old Part Number	BB-1138
Reference - Drawing Numbers	
Sales Drawing	SD-19016-004



Series image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free Status

Halogen-Free

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19016 Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Hand Crimp Tool	0640031200
Crimp Head for the	0640071200
AT-200™ Pneumatic	
Hand Tool	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION