




3M™ Bumpon™ Protective Products SJ5007 Black, 3000 per case

3M ID 70070107886 UPC# 00021200627286

Print Share



Network Access Message: The page

3M™ Bumpon™ Protective Product SJ5007 is a self-adhesive rubber bumper designed to be used as feet, stops and spacers. The flat top shape provides increased load bearing capacity and better wear resistance. Black, 0.413 in. wide x 0.100 in. high.

All 3M™ Bumpon™ Protective Products feature a plasticizer-free, urethane composition which exhibits:

- Easy application with 3M pressure sensitive adhesives.
- High skid-resistance.
- Won't scratch or stain surfaces.
- Reduces vibration and noise.
- Will not crack or harden.



Need Help?

Questions? We can help
[Contact Us](#)

Overview

Support

Suggested Applications

Use almost anywhere slamming, scratching, nicking, scuffing, marring, sliding, vibration, or noise could be a problem for your product.

- Feet on the bottom of small appliances, desktop or handheld electronic devices, electronic cabinetry, telephones, keyboards, foot pedals, scales, clocks, speakers, dispensers, and computers.
- Stops for cabinet doors, lids, and drawers.
- Spacers for picture frames to provide alignment; for electronics and automotive applications and aid in assembly.
- Protectors to prevent damage in shipping, and keep parts from direct contact with each other.

Specifications

Adhesive Type	Natural Rubber (R30)
Application	Notebook Computer Non-Skid Feet, Small Kitchen Appliance Feet - Recessed Application
Availability	Stocked
Backing Material	Polyurethane
Base Width	0.413 in
Base Width (metric)	10.4 mm
Color	Black
Hardness	72 Shore M
Height	0.100 Inch
Height (metric)	2.5 Millimetre
Height-Thickness Range	0.100 - 0.199 in
Height-Thickness Range (metric)	2.0 - 2.9 mm
Market Segment	Appliances, Electronics
Primary Liner	60# Super Calendered Kraft
Product Form	Molded
Product Series	SJ5007
Shape	Square-Tapered w/ Flat Top
Substrate	ABS, Acrylic, Glass, Metals, Polycarbonate, Polyethylene, Polypropylene, Wood
Width-Diameter Range	0.400 - 0.499 in
Width-Diameter Range (metric)	10.0 - 19.9 mm

Product Disclaimer

- The technical information and data shown on this page should be considered representative or typical only and should not be used for specification purposes.
- 3M products shown on this website may not be available in all geographic regions or may not be available at this time. Please contact your local sales representative to determine product availability.

