


EDSTLZ 1555



2-16 poles, Spacing 3.81 mm
insert required no. of poles **
How to order see page 6

Ratings:

*Approval pending



UL1059



CSA 22.2 No. 158



DIN VDE 0527


Rated Voltage	125 V ^B	150 V ^B	125 V
Rated Current	8 A	8 A	8 A (T60)
Test Voltage			1.39 kV

Dimensions

Spacing	3.81 mm
PCB Hole Diameter	1.2 mm

Materials

Insulating Material	PA
Flammability Class	UL94 V-0
Temperature Range	-30°C/+105°C
Contact Pin	Cu
Color	Green



P = No. of Poles