



LOC		DIST		ZONE		LTR		REV		DATE		APPRO	
G	14	P	F	E	REV 8	REDRAWN	PER 0720-0040-93	3-30-93	18	AMP			

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE		UL E13288 Listed	
16-14 AWG	SOLID OR STRANDED	16-14 AWG	SOLID OR STRANDED
16-14 AWG	SOLID OR STRANDED	NOT APPLICABLE	NOT APPLICABLE

1 STAMP AMP 16-14* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: NOT APPLICABLE
FOR ORDER ENTRY	1-800-526-5142	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS SOLID OR STRANDED

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC # - 3 PLC DEC # - ANGLES	DR 3-30-93 TA BRINKMAN CHK 3-30-93 DA PATTERSON APPD 3-30-93 DE MILLER APPD 3-30-93 JL MECKLEY PRODUCT SPEC FINISH TIN PLATE 0.00254 [0.00100] MIN THK PER MIL-T-10727
--	--

AMP	AMP Incorporated Harrisburg, PA 17105-3608
TERMINAL, RING TONGUE, FLAG, SOLISTRAND™	322819
SIZE 00779	CAGE CODE 00779
SCALE 10:1	DRAWING NO 322819
WEIGHT	SHEET 1 OF 1