

General Information

Extended Product Type:	A300-30-11 72V 50Hz / 84V 60Hz
Product ID:	1SFL551001R2311
EAN:	7320500213872
Catalog Description:	A300-30-11 72V 50Hz / 84V 60Hz Contactor

Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Across the Line Contactors

Ordering

EAN:	7320500213872
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85364900

Dimensions

Product Net Width:	140 mm
Product Net Depth:	180.500 mm
Product Net Height:	227 mm
Product Net Weight:	6.100 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	210 mm
Package Level 1 Length:	280 mm
Package Level 1 Height:	195 mm
Package Level 1 Gross Weight:	6.75 kg

Environmental

Ambient Air Temperature:	Close to Contactor Fitted with Thermal O/L Relay (0.85 - 1.1 U _c) -25 ... +55 °C Close to Contactor without Thermal O/L Relay (0.85 - 1.1 U _c) -25 ... +70 °C Close to Contactor for Storage -40 ... +70 °C
Maximum Operating Altitude Permissible:	3000 m
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical

Rated Operational Power AC-3 (P _e):	(220 / 230 / 240V) 90.0 kW (380 / 400V) 160.0 kW (415V) 160.0 kW (440V) 160.0 kW (500V) 200.0 kW (690V) 250.0 kW
Rated Operational Current AC-1 (I _e):	(690V) 40°C 500.0 A (690V) 55°C 400.0 A (690V) 70°C 325.0 A
Number of Main Contacts NO:	3
Number of Main Contacts NC:	0
Number of Auxiliary Contacts NO:	1
Number of Auxiliary Contacts NC:	1
Rated Control Circuit Voltage (U _c):	50 Hz 72 V 60 Hz 84 V
Terminal Type:	Screw Terminals

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SFA1-45;
RoHS Information:	1SFC101046D0203;

