

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35407-6702](#)
Status: **Active**
Description: 2.28mm Sealed Terminal, Female, 0.30-0.50mm² AVSS, 0.25mm Material Thickness, Pre-Tin Plated

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-35408-001 \(PDF\)](#)
[Packaging Specification PK-35407-003 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	35407
Application	Power
Crimp Quality Equipment	Yes
Product Name	N/A
UPC	800756627809
Physical	
Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.293/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.90mm max.
Wire Size AWG	20, 22
Wire Size mm ²	N/A

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35407-003
Product Specification	PS-35408-001
Sales Drawing	SD-35407-001




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[35407Series](#)

Mates With
[35420](#)

Use With
[35825](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for 2.28mm (.090") Sealed Receptacle Terminals	0638257600

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION