




MATERIALS:

Contact: Gold Plated Beryllium Copper

Spring: Stainless Steel

Body Insulation: Glass filled nylon.

RATINGS:

Voltage: Hands free testing in controlled voltage environments: 300 Vrms Max. *For CE compliance:* not intended for hand-held use at voltage above 33 Vrms/70 Vdc.

Operating Temperature: Max 302 F (150 C)

Current: 5 Amperes

ORDERING INFORMATION:

Model 4555-color* *Example:* to order a red 4555, the order number is 4555-2

*Colors:

0 (Black), 1 (Brown), 2 (Red), 3 (Orange), 4 (Yellow), 5 (Green), 6 (Blue), 7 (Violet), 8 (Gray), 9 (White)

Sold in packages of 10 per color.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA