





CCP / CCA  
Push Mount & Adhesive Clamp

- Specifications:
- Material: UL94 V-2 Nylon 6/6
  - Color: Grey

- Features:
- Two-stage lock design to accommodate different cable sizes in a single clamp
  - Easy to reopen with thumb tab release
  - Available in two styles: CCP for push mount into pre-drilled hole and CCA with a self adhesive backing



CCP Push Mount



CCA Adhesive



| Item No.   |          | A Bundle Ø Range |             | B     |       | C     |       | Mounting Hole Ø |      | Panel Thickness |           | Bulk Pack Qty. |
|------------|----------|------------------|-------------|-------|-------|-------|-------|-----------------|------|-----------------|-----------|----------------|
| Push Mount | Adhesive | In               | mm          | In    | mm    | In    | mm    | In              | mm   | In              | mm        |                |
| CCP001A    | CCA007A  | 0.230 - 0.280    | 6.0 - 7.0   | 0.787 | 20.00 | 0.984 | 25.00 | 0.187           | 4.80 | 0.070 - 0.110   | 1.8 - 2.8 | 100            |
| CCP002A    | CCA008A  | 0.280 - 0.310    | 7.0 - 8.0   | 0.787 | 20.00 | 0.984 | 25.00 | 0.187           | 4.80 | 0.070 - 0.110   | 1.8 - 2.8 | 100            |
| CCP003A    | CCA009A  | 0.350 - 0.390    | 9.0 - 10.0  | 0.984 | 25.00 | 1.181 | 30.00 | 0.187           | 4.80 | 0.070 - 0.110   | 1.8 - 2.8 | 100            |
| CCP004A    | CCA010A  | 0.470 - 0.550    | 12.0 - 14.0 | 0.984 | 25.00 | 1.181 | 30.00 | 0.187           | 4.80 | 0.070 - 0.110   | 1.8 - 2.8 | 100            |
| CCP005A    | CCA011A  | 0.620 - 0.710    | 16.0 - 18.0 | 0.984 | 25.00 | 1.181 | 30.00 | 0.187           | 4.80 | 0.070 - 0.110   | 1.8 - 2.8 | 100            |

WAC  
Webbed Adjustable Clip

- Specifications:
- Material: UL94 V-2 Nylon 6/6
  - Color: Natural

- Features:
- Locks securely and easily. Reopens for routing changes
  - Adjustable, ratcheting clip holds bundle securely in place
  - Spring in the top of the clamp adds additional tension to grip the bundle
  - Finger grip eases installation
  - Cupped base adds stability to the mounting and covers the hole completely




Figure 1




Figure 2




| Item No.     | D Bundle Ø |           | Mounting Hole Ø |           | Panel Thickness |           | Figure | Bulk Pack Qty. |
|--------------|------------|-----------|-----------------|-----------|-----------------|-----------|--------|----------------|
|              | In         | mm        | In              | mm        | In              | mm        |        |                |
| WAC1-01      | .12 - .34  | 3.0 - 8.5 | .157 - .189     | 4.0 - 4.8 | .019 - .063     | 0.5 - 1.6 | 1      | 1000           |
| WAC2-01      | .12 - .34  | 3.0 - 8.5 | .236 - .267     | 6.0 - 6.8 | .019 - .098     | 0.5 - 2.5 | 1      | 1000           |
| WAC3-01A4-RT | .12 - .34  | 3.0 - 8.5 | Adhesive        | Adhesive  | Adhesive        | Adhesive  | 2      | 1000           |

HLCC  
Hinged Locking Clamp

- Specifications:
- Material: Heat Stabilized UL94 V-2 Nylon 6/6
  - Color: Black


- Features:
- Securely holds corrugated/convoluted tubing or other bundles
  - An internal rib spanning the diameter of the clamp provides a tight grip
  - Releasable latch convenient for maintenance
  - Fir-tree mount accommodates a large range of panel thicknesses



| Item No. | Recommended Corrugated Tube Size |     |      |     | Mounting Hole Ø |           | Panel Thickness |           | A Ref. |     | B Ref. |      | Bulk Pack Qty. |
|----------|----------------------------------|-----|------|-----|-----------------|-----------|-----------------|-----------|--------|-----|--------|------|----------------|
|          | I.D.                             |     | O.D. |     | In              | mm        | In              | mm        | In     | mm  | In     | mm   |                |
| HLCC-1BK | .20                              | 5.0 | .28  | 7.1 | .26 - .28       | 6.5 - 7.0 | .03 - .12       | .08 - 3.0 | .23    | 5.8 | .28    | 7.2  | 1000           |
| HLCC-2BK | .27                              | 6.9 | .39  | 9.9 | .26 - .28       | 6.5 - 7.0 | .03 - .12       | .08 - 3.0 | .33    | 8.3 | .39    | 10.0 | 1000           |

KKR  
Adhesive Mount Clamp

- Specifications:
- Material: UL94 V-0 PVC
  - Color: Grey



| Item No.   | A Bundle Ø |      | B     |      | C     |      | Max Capacity D |      | Bulk Pack Qty. |
|------------|------------|------|-------|------|-------|------|----------------|------|----------------|
|            | In         | mm   | In    | mm   | In    | mm   | In             | mm   |                |
| KKR-5A1-RT | 0.521      | 13.2 | 0.750 | 19.1 | 0.750 | 19.1 | 0.680          | 17.3 | 500            |