

PART NAME	UTILIBOX (STYLE E)	PART No.	CU-789-MB TD CU-792-MB
-----------	--------------------	----------	------------------------

MATERIAL:
ABS THERMOPLASTIC
FLAMMABILITY RATING OF 94V-0 AT
0.070" THICKNESS AND CONTINUOUS
USE TEMPERATURE OF 70° C.)

FINISH:
BODY - OUTSIDE SURFACES ARE TEXTURED FINISH
WITH TEXTURED INSERT AREA.
COVER - SURFACES ARE SMOOTH.


COLOR: BLACK

NOTE: ALL DIMENSIONS HAVE ± 0.010 TOLERANCE
UNLESS OTHERWISE SPECIFIED.

COVER REDUCES INSIDE HEIGHT BY 0.075.

LENGTH AND WIDTH DIMENSIONS ARE
TAKEN FROM CLOSED END OF THE BOX.
DIMENSIONS INCREASE SLIGHTLY AT
OPEN END DUE TO TAPER.

FOUR (4) #4 x 0.500" LG. SELF THREADING
SCREWS WITH HI/LOW THREADS
ARE SUPPLIED FOR MOUNTING COVER.



PART No.	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T
CU-789-MB	3.000	2.000	0.900	2.047	3.875	2.468	1.234	1.468	0.734	2.790	1.781	3.500	1.039	2.968	1.968	1.750	0.984	0.609
CU-790-MB	3.000	2.000	1.500	2.079	3.875	2.468	1.234	1.468	0.734	2.790	1.781	3.500	1.039	3.000	2.000	1.750	1.000	0.625
CU-791-MB	3.000	3.000	1.500	3.079	3.875	2.468	1.234	2.468	1.234	2.790	2.781	3.500	1.539	3.000	3.000	1.750	1.500	0.625
CU-792-MB	4.000	1.750	1.000	1.802	4.875	3.468	1.734	1.218	0.609	3.790	1.531	4.500	0.901	3.978	1.733	3.000	0.866	0.489