




FO-55111-A

HONEYWELL
PART NUMBER

341SM2-T

PRODUCT CODE
TZA2918

REV	DOCUMENT	CHANGED BY	CHECK
10	0041782	PK 21JUL08	ASD



NOTE -

⚠ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø .087 MAX ON .375±.002 CENTERS

2- SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

3 TERMINALS ARE PLATED FOR SOLDERING

RELEASE NO. PR - 8439

REPLACES -

CHARACTERISTICS

OPERATING FORCE --- 30 GRAM MAX

RELEASE FORCE--- 5 GRAM MIN

DIFFERENTIAL TRAVEL--- .027 MAX

OVERTRAVEL - - - - .026 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT SPDT			
APPROVALS	KEMA, CE	11A 250V ~ T85 1E4 5A 30 Vdc T85 1E4	CE
	UL, CSA	11A 1/4 HP 125 250 VAC 5A 30 VDC	BRAND L190

DESIGN UNITS: INCH			
TOLERANCES UNLESS NOTED:			
NO PLACE	X	±	
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	
ANGLES		±	
THIRD ANGLE PROJECTION			

DRAWN	VK	03 DEC 07
CHECK	RJ	03 DEC 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE			
SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	341SM2-T	10
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1