




SLEEVE

SERRATIONS

BODY

1

3.68±0.08
[.145±.003]
FOR #6 STUD

7.54
[.297]

5.15 [.203]
MIN

5

15.72 [.619] MAX

19.43 [.765] MAX

1

STAMP AMP 16-14* LOCATE APPROX AS SHOWN

2. WIRE INSUL DIA., 3.00-4.90 [.118-.193]

3. TONGUE MATL THK, 0.79 ±0.05 [.031±.002]

4

MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - BLUE

5

APPLIES FROM THE METAL EDGE OF BARREL TO THE CENTER OF THE STUD HOLE

5000	ON TAPE, REEL	54367-2
500	LOOSE PIECE	54367-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C [221° F]

VOLTAGE RATING:
600V MAX
(1000V FIXTURE OR SIGN)

CIRCULAR MIL AREA:
1.04-2.62mm² [2,050-5,180]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.20 [.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

MATERIAL

- 4

DWN

L OLMEDA

03NOV94

CHK

M ELLIS

03NOV94

APVD

G NGO

03NOV94

PRODUCT SPEC

UL486A

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

Tyco

Electronics

Tyco Electronics Corporation

Harrisburg, Pa 17105-3608

NAME

TERMINAL, SPADE,
PLASTI-GRIP,
WIRE SIZE: 16-14

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-54367

RESTRICTED TO

-

SCALE

6:1

SHEET

1

OF

1

REV

G1

AMP 1470-19 REV 31MAR2000