



UPC Code : 078477073735

Country Of Origin : Mexico

MS602-BW

60 Amp, 600 Volt, Single Phase, Toggle Double-Pole AC Manual Motor Controller, Industrial Grade, Non-Grounding, Back Wired, - Black

Powerswitch® Industrial Grade AC Manual Motor Controllers provide safe, reliable control of a variety of motor loads. Typical applications include manual ON/OFF switching control of conveyor systems, pumping machines, HVAC systems, air compressors and other heavy manufacturing equipment. These motor controllers are available for both single-phase and three-phase applications.

Technical Information

AC Horsepower Ratings

HP Rating : 10HP-240V 15HP-480V
20HP-600V

Electrical Specifications

Amperage : 60 A

Dielectric Voltage : Withstands 2200V for 1 min.

Endurance : 6,000 cycles inductive motor type load

Grounding : Non-Grounding

Pole : 2

Temperature Rise : 50°C Max at full rated current

Voltage : 600 VAC

Environmental Specifications

Flammability : Rated V-0 per UL 94

Operating Temperature : -40°C to 60°C

Material Specifications

Base Material : Thermoplastic Polyester

Color : Black

Contacts : .046" Thick Silver-Cadmium Oxide

Face Material : Thermoplastic Polyester

Strap Material : Nickel-Plated Brass

Terminal Screws : Zinc-Plated Steel, Triple Combination

Toggle : Thermoplastic Polyester

Yoke : Nickel-Plated Brass

Mechanical Specifications

Product ID : Ratings are permanently marked on device

Terminal Accom. : 10-4 AWG

Terminal ID : T1, T2, T3, L1, L2 & L3 marked on back of device

Termination : Back

Torque Range : 25 inch pounds maximum

Product Features

Actuator Material : Valox

Body Material : Rynite

Color : Black

Device Type : Toggle Switch

Standards and Certifications : UL/CSA

Strap Material : Nickel-Plated Brass

Warranty : 10-Year Limited

Standards and Certifications

ANSI : C-73


NEMA : WD-1 & WD-6

NOM : NOM-ANCE


UL 60947-4-1 : supersedes UL 508

Warranty : 10-Year Limited

cUL per CSA C22.2 No. 111 : File #E63969



Wiring Diagram Double Pole



SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
JOB NUMBER:		

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):
+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·
FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-
1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:
www.leviton.com/international/contacts/

