


[About Leviton](#)
[A Century of Success](#)
[Press](#)
[Join Our eMailing List](#)
[Trade Shows](#)
[RoHS](#)
[Career Opportunities](#)
[Contact Us](#)
[All Leviton Products](#)
[Electrical](#)
[Network Solutions](#)
[Lighting Controls](#)
[Entertainment](#)
[Home Automation](#)
[Connected Home](#)
[Energy Management](#)
[Power Quality](#)
[Library Home](#)
[Application Notes](#)
[Brochures / Catalogs](#)
[Case Studies](#)
[DDLs](#)
[Downloads](#)
[Drawings](#)
[Line Cards](#)
[Manuals / Instructions](#)
[Product Specifications / Datasheets](#)
[Software](#)
[Specs \(AIA / CSI\)](#)
[Take One](#)
[Tech Notes](#)
[Technical Articles](#)
[Videos](#)
[ez-Biz](#)
[ez-Find](#)
[ez-Learn](#)
[ez-Configurator](#)
[Distribution Home](#)
[Contractor Connection](#)
[ez-Learn](#)
[ez-Find](#)
[Sign In - B2B](#)
[OEM Home](#)
[How to Buy](#)
[Whats New](#)
[Press/News](#)
[Retail Home](#)
[Product Information](#)
[How To](#)
[Merchandising](#)
[Energy Smart Living](#)
[International Home](#)
[China \(English\)](#)
[China \(Chinese\)](#)
[Mexico \(English\)](#)
[Mexico \(Spanish\)](#)
[Middle East \(English\)](#)
[International Contact](#)
[Press](#)
[Products](#)
[Trade Shows](#)
[Made to Order](#)
[EZE-Rough](#)
[Acenti Devices](#)
[AC Switches](#)
[Appliance Switches](#)
[Architectural Controls](#)
[Camera Systems](#)
[Combination Devices](#)
[Connectors & Cables](#)
[Cord Sets](#)
[Corrosion Resistant Devices](#)
[Daylighting Controls](#)
[Decora Devices](#)
[Dimmers](#)
[Cam-Type Devices](#)
[Electrical Accessories](#)
[Entertainment Accessories](#)
[Entertainment Fixtures](#)
[Entertainment Lighting Controls](#)
[Entertainment Lighting Kits](#)



[Electrical](#)
[Network Solutions](#)
[Lighting Controls](#)
[Entertainment](#)
[Home Automation](#)
[Connected Home](#)
[Energy Management](#)
[Power Quality](#)


[ZOOM](#)

Quantity:

Color: Yellow



NEMA: 5-15R



5256-VY

Description

15 Amp, 125 Volt, NEMA 5-15P, 2P, 3W, Plug, Straight Blade, Industrial Grade, Grounding, Python - Yellow

Additional Product Information

- [Dimensional Drawing](#)
- [Wiring Diagram](#)

Product Features

Grounding: Grounding
Feature: Python
Amperage: 15 Amp
Voltage: 125 Volt
NEMA: 5-15R
Pole: 2
Wire: 3
Cord Range: .250 - .650
Wire Gauge: 18-10 AWG
Blades/Contacts: Solid Brass
Body Material: Nylon
Assembly Screws: Steel, Zinc Plated
Color: Yellow
Standards and Certifications: UL/CSA
Warranty: 2 Year Limited

Features and Benefits

- Tough high-impact body
- Hinged design delivers fast, easy installation and assembly
- Triple-drive screws for easy wiring - Standard, Phillips, Robertson
- Wide Cord Clamp Range, 18-3 SVT-10-3 ST, (.250"-.650")
- Backed by a 2-Year Warranty

Electrical Specifications	
Temperature Rise:	Max 30C after 250 cycles OL at 200 percent rated current
Dielectric Voltage:	Withstands 2000V per UL498
Current Interrupting:	Certified for current interrupting at full rated current

Environmental Specifications	
Flammability:	Rated V-2 per UL94
Operating Temperature:	-40C to 60C

Material Specifications	
Body Material:	Nylon
Blades/Contacts:	Brass
Assembly Screws:	Steel, Zinc Plated

Mechanical Specifications	
Product ID:	Ratings and NEMA I.D. permanently marked on device
Terminal Accom.:	18-10 AWG
Terminal ID:	Brass-Hot, Green-Ground, Silver-Neutral
Cord Range:	.250 - .656

Standards and Certifications	
NEMA:	WD-6
ANSI:	C-73
UL:	Listed
CSA C22.2 No. 42:	File LR-406
NOM:	057