


Packaging

● Ammo-pack (Flat box type)



(mm)				
L	H	W	Case Size ($\phi D \times L$)	Q'ty / Box
340	150	50	3 × 5	2,000
340	200	50	4 × 5, 4 × 7	2,000
340	250	50	5 × 5, 5 × 7	2,000
			8 × 5, 8 × 7, 8 × 8	1,000
340	300	50	6.3 × 5, 6.3 × 6, 6.3 × 7	2,000
340	260	54	4 × 11, 5 × 9, 5 × 11, 5 × 15	2,000
			8 × 9, 8 × 10, 8 × 11.5, 8 × 12, 8 × 15	1,000
340	200	54	10 × 8, 10 × 9, 10 × 10, 10 × 12.5, 10 × 13, 10 × 15, 10 × 16	500
340	300	54	6.3 × 9, 6.3 × 10.5, 6.3 × 11, 6.3 × 15	2,000
340	260	62	8 × 20	1,000
340	200	62	10 × 20	500
340	200	65	10 × 25	500
330	290	65	12.5 × 12.5, 12.5 × 15, 12.5 × 20	500
			12.5 × 25	250
320	230	65	18 × 15, 18 × 20, 18 × 25	250

● Axial lead type (Applicable standard JIS C0805)

The following code shall be put at 12th to 14th digit of the corresponding type number of capacitors.

Taping Specifications		Case dia (ϕ)	Taping code	Q'ty / Reel (pcs.)
Dim. W (Tape distance)	Dim. P (Component Pitch)			
52.4	10	5	1LS	1,600
		6.3		1,300
		8		1,000
63.5	10	5	1LV	1,600
		6.3		1,300
		8		1,000
73.0	10	5	1LY	1,600
		6.3		1,300
		8		1,000
52.4	15	10	1LT	500
		13 (except 31.5L)		350
63.5	15	10	1LW	500
		13		350
73.0	15	10	1LZ	500
		13		350

Please contact us for complete information on the package dimensions for tapes axial lead capacitors.

