

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

J

REDRAWN PER 0G3A-0249-01

03APR01

JR

TM

1

2

3

4

STAMPED AMP 22-18*, APPROX AS SHOWN.

22-16 TERMINALS ARE STAMPED 22-18 IN

ACCORDANCE WITH MILITARY SPEC MIL-T-7928

COMMERCIAL WIRE RANGE 22-16

FOR .105 TO .140 WIRE INSULATION DIA.

TONGUE MATERIAL THK IS .031±.002.

PRELIMINARY - NOT FOR PRODUCTION

INSULATION

SERRATIONS

BODY

SLEEVE

.031 MIN

.904 MAX

.125

.140

1

100	LOOSE PIECE, BOX	8-34294-1	BODY: COPPER PER ASTM B152 TIN PLATE PER ASTM B545 SLEEVE: COPPER PER ASTM B152 TIN PLATE PER ASTM B545 INSULATION: NYLON, COLOR - RED					
5000	ON TAPE, REEL	2-34294-1						
1000	LOOSE PIECE	34294						
QTY	PACKAGE TYPE	PART NO.	MATERIAL & FINISH					
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN JR RUTH 03APR01 CHK MS FEHER 03APR01 APVD T MICHELUTTI 03APR01 PRODUCT SPEC — APPLICATION SPEC — WEIGHT —					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME WIRE TERMINAL, PIDG, RECTANGULAR TAB, WIRE SIZE: 22-16					
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±.008 4 PLC ±- ANGLES ±5°						
MATERIAL —		FINISH —	SIZE A3	CAGE CODE 00779	DRAWING NO C- 34294	RESTRICTED TO —		
CUSTOMER DRAWING						SCALE 8:1	SHEET 1 OF 1	REV J

AMP 1470-19 REV 11JUN97

03-APR-01 14:21:05 amp13469 /home/amp13469/u.new