



**SLB-1 thru 7**



**SOLB-8, 9, 0**



**SLBM-4**



**MLB-12**

- Suitable for wet locations when used with gasketed covers.
- Federal Specification W-C-586D / A-A 50563.
- Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b), Class I, Div. 2, (Suitable for use in Class I Zone 2 applications) 502.10 and 503.10.



Listed - File E22698



Certified - File LR11852

See files for details or call Killark

## FEATURES-SPECIFICATIONS

### Features



- Designed for easier wire pulling
- Includes Cover and Gasket

### Material/Finish

#### Copper-free Aluminum

(less than 4/10 of 1%)

- Electrostatically applied powder coating



| SERVICE ENTRANCE BODIES |              |                   |                   |                   |                   |                  |                  |
|-------------------------|--------------|-------------------|-------------------|-------------------|-------------------|------------------|------------------|
| CATALOG NUMBER          | CONDUIT SIZE | A                 | B                 | C                 | D                 | E                | F                |
| SLB-1                   | 1/2"         | 2-3/4"<br>(70)    | 1-1/16"<br>(27)   | 2-3/8"<br>(60)    | 3/4"<br>(19)      | 1-3/8"<br>(35)   | 1-3/16"<br>(30)  |
| SLB-2                   | 3/4"         | 3-1/8"<br>(79)    | 1-3/8"<br>(35)    | 2-11/16"<br>(68)  | 7/8"<br>(22)      | 1-11/16"<br>(43) | 1-3/8"<br>(35)   |
| SLB-3                   | 1"           | 3-3/4"<br>(95)    | 1-5/8"<br>(41)    | 3-1/4"<br>(83)    | 15/16"<br>(24)    | 1-15/16"<br>(49) | 1-3/4"<br>(44)   |
| SLB-4                   | 1-1/4"       | 5"<br>(127)       | 2"<br>(51)        | 4-5/16"<br>(110)  | 1-1/4"<br>(32)    | 2-1/2"<br>(64)   | 2-3/16"<br>(56)  |
| SLBM-4                  | 1-1/4"       | 7-1/4"<br>(184)   | 1-15/16"<br>(49)  | 6-3/8"<br>(162)   | 15/16"<br>(24)    | 2-5/8"<br>(67)   | 2-1/2"<br>(64)   |
| SLB-5                   | 1-1/2"       | 5-3/4"<br>(147)   | 2-7/16"<br>(62)   | 4-3/4"<br>(121)   | 1-1/2"<br>(38)    | 2-9/16"<br>(65)  | 2-7/16"<br>(62)  |
| SLB-6                   | 2"           | 6-1/4"<br>(159)   | 2-15/16"<br>(75)  | 5"<br>(127)       | 1-5/8"<br>(41)    | 3-1/8"<br>(79)   | 2-13/16"<br>(71) |
| SLBM-6                  | 2"           | 9-1/2"<br>(241)   | 2-11/16"<br>(68)  | 8-9/16"<br>(217)  | 11-3/16"<br>(284) | 3-7/16"<br>(87)  | 3-1/8"<br>(79)   |
| SLB-7                   | 2-1/2"       | 8"<br>(203)       | 3-9/16"<br>(90)   | 6-7/8"<br>(175)   | 11-5/16"<br>(287) | 4"<br>(102)      | 3-1/2"<br>(89)   |
| SOLB-8                  | 3"           | 12-1/4"<br>(311)  | 4-7/16"<br>(113)  | 10-7/16"<br>(265) | 11-3/16"<br>(284) | 6-1/4"<br>(159)  | 4-7/16"<br>(113) |
| SOLB-9                  | 3-1/2"       | 15"<br>(381)      | 5"<br>(127)       | 11-7/8"<br>(302)  | 3-1/8"<br>(79)    | 7-1/2"<br>(191)  | 5-1/2"<br>(140)  |
| SOLB-0                  | 4"           | 15"<br>(381)      | 5"<br>(127)       | 11-7/8"<br>(302)  | 3-1/8"<br>(79)    | 7-1/2"<br>(191)  | 5-1/2"<br>(140)  |
| MLB-12                  | 5"           | 42-1/2"<br>(1080) | 8-11/16"<br>(221) | 38-5/8"<br>(981)  | 4-5/8"<br>(118)   | 12-1/4"<br>(311) | 9"<br>(229)      |



**KILLARK®**