






Technical drawing of a mechanical part showing dimensions and tolerances. The drawing includes the following specifications:

- $\varnothing 0.89 \pm 0.08$  [0.035  $\pm$  .003] 8 PLACES
- POSITION 1
- POSITION 8
- $10.16 \pm 0.05$  [.400  $\pm$  .002]
- $2.54 \pm 0.05$  [.100  $\pm$  .002] TYPICAL
- $1.27 \pm 0.05$  [.050  $\pm$  .002] TYPICAL
- $2.54 \pm 0.05$  [.100  $\pm$  .002]
- $6.35 \pm 0.05$  [.250  $\pm$  .002]
- $2.03 \pm 0.05$  [.080  $\pm$  .002] 2 PLACES
- $11.43 \pm 0.05$  [.450  $\pm$  .002]
- $\varnothing 3.25 \pm 0.08$  [.128  $\pm$  .003] 2 PLACES (3)
- $3.05 \pm 0.05$  [.120  $\pm$  .002] 2 PLACES
- $\varnothing 1.57 \pm 0.08$  [.062  $\pm$  .003] 2 PLACES



SUGGESTED PC BOARD LAYOUT  
COMPONENT SIDE (TOP)  
SCALE 4:1

|                                                                                                                                                                                     |  |                                                                                                                                                           |  |                                                                                                                             |  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.<br>IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING<br>ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. |  | DWN 090CT95<br>T. SPRINKLE<br>CHK 10JAN97<br>C. WHITT<br>APVD 10JAN97<br>J. TONEY<br>PRODUCT SPEC<br>108-1163<br>APPLICATION SPEC<br>114-2048<br>WEIGHT - |  | <b>AMP</b><br>AMP Incorporated<br>Harrisburg, PA 17105-3608                                                                 |  |
| DIMENSIONS:<br>mm [INCHES]                                                                                                                                                          |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>0 PLC ±-<br>1 PLC ±-<br>2 PLC ±0.25 [.013]<br>3 PLC ±0.13 [.005]<br>4 PLC ±-<br>ANGLES ±-<br>MATERIAL FINISH |  | NAME<br>MODULAR JACK ASSEMBLY,<br>SINGLE PORT, 8 POSITION, SHIELDED,<br>REVERSE PANEL GROUND TABS, CATEGORY 5<br>SIZE<br>A2 |  |
|                                                                                                |  | DRAWING NO<br>C-406296                                                                                                                                    |  | SCALE 2:1<br>SHEET 1 of 1<br>REV F                                                                                          |  |
|                                                                                                |  |                                                                      |  | CUSTOMER DRAWING                                                                                                            |  |