

5

4

3

2

1

Mating face according to : MIL-C24308 / DIN 41652 / CECC 75301-802

No.1 contact

nut thread

2.9 ± 0,3

Printed board layout
component side

63,5

0,6

6,2

63,5 ± 0,1

69,7 max.

No.19 contact

2,84

1,42

18 x 2,76 = 49,68

17 x 2,76 = 46,92

2,76

Ø 3,1 ± 0,1

Ø 0,1

No.1 contact

No.37 contact

2,76

Ø 1 ± 0,1

Ø 0,05

No.20 contact

09 66 411 3501

M3

1

09 66 411 6501

M3

2

09 66 411 7501

M3

3

09 66 411 3502

4-40 UNC

1

09 66 411 6502

4-40 UNC

2

09 66 411 7502

4-40 UNC

3

Part number

Nut thread

Performance level

Mod.

Dat.

Name

Dat.

Name

Detail.

05/03/02

CV

Insp.

Stand.



All Dim. in mm
Orig. Size DIN A 4

D-sub, 37 poles,
female, straight,
with solder pins 2.9,
and nuts.

Maßstab/
Scale

1,5:1

HARTING EURL
F-95972 Paris



TB 09 66 411 x50x

Sub.

Blatt/ Page

2