




Basic data

Application
 Scope of delivery

Use with sensors Ø18mm and M18
 Clamp holder (1x)
 Nut DIN 1763 M24x1.5 (2x)

Mechanical data

Dimensions
 Mounting type
 Tightening torque
 Tightening torque for clamping

30.0 mm x 36.0 mm
 screwing/clamping
 25 Nm
 4.0 Nm

Material
 Surface protection

CuZn
 Nickel-plated

Remarks

The fixed stop may alter the switching distance of the proximity switch.
 The proximity switch is inserted into the clamp holder up to the fixed stop and secured using a pressure screw.
 For proximity switches from fixing length 30 mm

Definitions see general catalog

Subject to change without notice.

00000000000000/552168/000000000