


SMALL SIGNAL TRANSISTORS



TO 72



TO 39

Polar.	Max ratings			Type	Characteristics				Package
	V_{CE0} (V)	I_C (mA)	P_{tot} (mW)		f_T (MHz)	NF (dB)	P_G (dB)	@ f (MHz)	
NPN	15	25	200	BFY90	1400	4.5	8	800	TO-72
NPN	15	50	200	2N918	900	3.5	22	200	TO-72
NPN	15	50	200	BFX73	900	6	-	60	TO-72
PNP	25	50	225	BFR99A	2300	3.5	8	800	TO-72
NPN	20	200	600	2N3137	750	-	7	250	TO-39
NPN	30	200	800	BFR36	1000	4	16	200	TO-39
NPN	20	400	1000	2N5109	1400	3	14	200	TO-39

SOLID STATE RELAYS

Type	Description	Package
LH1056	Optically coupled high voltage solid state AC/DC relay	6-LEAD MINIDIP
LH1061	Optically coupled high voltage solid state AC/DC relay	SPECIAL MINIDIP

LOCAL AREA NETWORK

Type	Description	Package
MK5030	Starlan HUB	DIP48
MK5032	Local Area Network Controller for Ethernet (LANCE) and Starlan	DIP48
MK5033	Manchester encoder/decoder	DIP28
MK5035	Starlan Station	DIP20
MK50351	Starlan Station compatible with MK5032	DIP20
MK68592	Serial Interface Adapter/Manchester encoder/decoder for Ethernet (300 mil)	DIP24

PACKET SWITCHING

Type	Description	Package
MK5025	X.25 LAPB/ISDN LAPD/HDLC CMOS Hi-speed link level controller with DMA	DIP48, PLCC52

FILTERS

See chapter «ANALOGUE CELLS AND ARRAYS»