




Notes:

- Insulator: PBT, UL94V-0
- Contacts: Phosphor bronze, Tin
- Current Rating: 1A
- Insulating resistance: 10000MΩ min
- Withstanding voltage: 1000V AC
- Contact resistance: 15mΩ max
- Operating Temperature: -40°C to +105°C

No. of Contacts	Quantity in tube	Dimension					
		A	B	C	D	E	F
20	39	15,34	15,34	5,08	5,08	10,03	10,03
28	33	17,85	17,85	7,62	7,62	12,57	12,57
32	29	17,85	20,42	7,62	10,16	12,57	15,11
44	26	23,07	23,07	12,70	12,70	17,65	17,65
52	23	25,50	25,50	15,24	15,24	20,19	20,19
68	19	31,00	31,00	20,32	20,32	25,27	25,27
84	16	36,10	36,10	25,40	25,40	30,35	30,35

RoHS
Compliant

ITEM NO
A-CCSXX-Z-SM-R

TITLE
Chip-Carrier PLCC Socket, Tin, SMD

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 – Tempe, AZ 85283
Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED
© Copyright 2008 by Assmann Electronic Components
All International Rights Reserved