


THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.




LED POLARITY			
PIN 9	PIN 10	PIN 11	COLOR
-	+		GREEN
	+		YELLOW


ELECTRICAL CHARACTERISTICS @ 25°C

URNS RATIO	1CT : 1CT ±3%		
□CL @ 0.1V, 100KHz	350μH MIN.		
8mA DC BIAS			
INSERTION LOSS	-1.1 dB		
100KHz TO 100MHz			
RETURN LOSS (MIN.)	-18 dB		
1MHz-30MHz			
60MHz-80MHz	-12 dB		
XTALK	-35 dB MIN.		
100KHz TO 100MHz			
LED			
VF (FORWARD VOLTAGE)	IF=20mA	YELLOW GREEN	2.2V TYP.
		YELLOW	2.1V TYP.
λD (DOMINANT WAVELENGTH)	IF=20mA	YELLOW GREEN	565nm TYP.
		YELLOW	590nm TYP.
HIPOT (Isolation Voltage):	1500 Vrms or 2250VDC		



ORIGINATED BY	DATE	TITLE 2X8 MagJack® with LED 0810-2H8R-28-F	PART NO. / DRAWING NO.	STANDARD DIM.		[] METRIC DIM. AS REFERENCE		 COMPONENTS FOR A CONNECTED PLANET
CHUNG	01-18-07		08102H8R28-F	TOL. IN INCH		UNIT : INCH [mm]	REV. : A	
DRAWN BY	DATE		FILE NAME	.X		SCALE : N/A	SIZE : A4	
DE	01-18-07		08102H8R28-FA.DWG	.XX			PAGE : 2	
			.XXX					

THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.



NOTES:


- PLASTIC HOUSING: THERMOPLASTIC PBT
FLAMMABILITY RATING UL 94V-0
CONTACT PLATING: 30 MICRO-INCH HARD GOLD PLATING
OUTPUT PINS: TIN-COATED COPPER WIRE, DIA 0.018 INCH.
METAL SHIELD: NICKEL PLATED ON COPPER ALLOY.
(ALL GROUND LEADS ARE SOLDER DIPPED)

1. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
2. MARK PART WITH MFG. LOGO; MFG. NAME; PART NUMBER; DATE CODE.

3. RoHS COMPLIANCE, PER EU DIRECTIVE 2002/95/EC.




PORT 2
LED 2.
LOWER DECK
GREEN/YELLOW
RJ45 1
PORT 1



2

1

PORT 16
LED 1.
UPPER
DECK
GREEN/
YELLOW
RJ45 1
PORT 15




0.550 [13.97]
TYPICAL

ORIGINATED BY	DATE	TITLE	PART NO. / DRAWING NO.	STANDARD DIM.		[] METRIC DIM. AS REFERENCE	
				TOL. IN INCH		UNIT : INCH [mm]	REV. : A
QIN/BILL	01-18-07	2X8 MagJack® with LED 0810-2H8R-28-F	08102H8R28-F	.X		SCALE : N/A	SIZE : A4
DRAWN BY	DATE		FILE NAME	.XX			PAGE : 3
TING	01-18-07		08102H8R28-FA.DWG	.XXX	±0.010		




THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.



PIN-OUT INFORMATION
(COMPONENT SIDE VIEW)

11	YELLOW LED CATHODE
10	COMMON ANODE
9	GREEN LED CATHODE
8	GND
7	TCT
6	TD-
5	NC
4	RCT
3	TD+
2	RD-
1	RD+


PORT ASSIGNMENT
(COMPONENT SIDE VIEW)



THE SHADED AREA ON THE CUSTOMER BOARD ARE RECOMMENDED TO BE CLEAR OFF ANY VIA HOLE OR COMPONENT PAD.

ORIGINATED BY	DATE	TITLE 2X8 MagJack® with LED 0810-2H8R-28-F	PART NO. / DRAWING NO. 08102H8R28-F		STANDARD DIM. TOL. IN INCH		[] METRIC DIM. AS REFERENCE		 COMPONENTS FOR A CONNECTED PLANET
QIN/BILL	01-18-07		FILE NAME 08102H8R28-FA.DWG	.X		UNIT : INCH [mm]		REV. : A	
DRAWN BY	DATE			.XX		SCALE : N/A		SIZE : A4	
TING	01-18-07			.XXX	±0.004			PAGE : 4	

THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.




SUGGESTED FOOTPRINT
(COMPONENT SIDE VIEW)

ORIGINATED BY QIN/BILL	DATE 01-18-07	TITLE 2X8 MagJack® with LED 0810-2H8R-28-F	PART NO. / DRAWING NO. 08102H8R28-F	STANDARD DIM. TOL. IN INCH		[] METRIC DIM. AS REFERENCE	
				.X		UNIT : INCH [mm]	REV. : A
DRAWN BY TING	DATE 01-18-07		FILE NAME 08102H8R28-FA.DWG	.XX		SCALE : N/A	SIZE : A4
				.XXX	±0.004		PAGE : 5



THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.



NOTES:

THE DISTANCE OF PANEL INSIDE SURFACE RELATIVE TO FRONT SURFACE OF PART IS ONLY A SUGGESTION. IN CASE THIS DISTANCE IS DIFFERENT, THE REQUIRED PANEL OPENING DIMENSIONS CHANGE ACCORDINGLY.

PACKING INFORMATION

PACKING TRAY : 0200-9999-B2 (TOP)
0200-9999-B3 (BOTTOM)

PACKING QUANTITY : 10 PCS FINISHED GOODS PER TRAY
7 TRAYS (70 PCS FINISHED GOODS) PER CARTON BOX

NOTE : CARDBOARDS ARE PLACED BETWEEN LAYERS OF PACKING TRAY INSIDE CARTON BOX
(INCLUDE THE UPPERMOST AND LOWERMOST TRAY)

ORIGINATED BY QIN/BILL	DATE 01-18-07	TITLE 2X8 MagJack® with LED 0810-2H8R-28-F	PART NO. / DRAWING NO. 08102H8R28-F	STANDARD DIM. TOL. IN INCH		[] METRIC DIM. AS REFERENCE	
				.X		UNIT : INCH [mm]	REV. : A
DRAWN BY TING	DATE 01-18-07		FILE NAME 08102H8R28-FA.DWG	.XX		SCALE : N/A	SIZE : A4
				.XXX	±0.004		PAGE : 6

