


80 Plus Bronze Power Supply



Model Name	PS8-300ATX-ZBE	PS8-400ATX-ZE	PS8-500ATX-ZE	PS8-700ATX-ZE
Wattage	300 W	400 W	500 W	700 W
Input Range	100 ~ 240 V _{AC} 47 ~ 63 Hz 8 ~ 4 A	100 ~ 240 V _{AC} 60 ~ 50 Hz 8 ~ 4 A	100 ~ 240 V _{AC} 60 ~ 50 Hz 8 ~ 4 A	100 ~ 240 V _{AC} 60 ~ 50 Hz 12 ~ 6 A
Outputs	+3.3 V @ 16 A, +5 V @ 19 A +12 V @ 11 A, +12 V _{cpu} @ 11.5 A -12 V @ 0.3 A -5 V @ 0.3 A, +5 V _{sb} @ 2 A	+3.3 V @ 21 A, +5 V @ 20 A +12 V1 @ 16 A, +12 V2 @ 16 A -12 V @ 0.5 A -5 V @ 0.3 A, +5 V _{sb} @ 3 A	+3.3 V @ 24 A, +5 V @ 20 A +12 V1 @ 16 A, +12 V2 @ 16 A -12 V @ 0.5 A -5 V @ 0.3 A, +5 V _{sb} @ 3 A	+3.3 V @ 24 A, +5 V @ 30 A +12 V1 @ 16 A, +12 V2 @ 16 A +12 V3 @ 16 A, +12 V4 @ 16 A -12 V @ 0.5 A -5 V @ 0.5 A, +5 V _{sb} @ 4 A
MTBF (hrs)	100,000 @ 25° C	100,000 @ 25° C	100,000 @ 25° C	100,000 @ 25° C
Dimensions (H x W x D)	86 x 150 x 140 mm (3.39" x 5.91" x 5.51")	86 x 150 x 140 mm (3.39" x 5.91" x 5.51")	86 x 150 x 140 mm (3.39" x 5.91" x 5.51")	86 x 150 x 140 mm (3.39" x 5.91" x 5.51")
Safety	UL, TUV, CB, CCC	UL, TUV, CB, CCC	UL, TUV, CB, CCC	UL, TUV, CB, CCC
Compatible Chassis	IPC-602, IPC-510, IPC-610, IPC-611, IPC-619(S) ACP-2000, ACP-4000, ACP-4010, ACP-4320, ACP-4360 IPC-6606, IPC-6608, IPC-5122 IPC-7130, IPC-7132	IPC-602, IPC-510, IPC-610, IPC-611, IPC-619(S) ACP-2000, ACP-4000, ACP-4010, ACP-4320, ACP-4360 IPC-6606, IPC-6608, IPC-5122 IPC-7130, IPC-7132	IPC-610, IPC-611, ACP-4000, ACP-4010, ACP-4320, ACP-4360	IPC-610, IPC-611, ACP-4000, ACP-4010, ACP-4320, ACP-4360