


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL INTERNATIONAL RIGHTS RESERVED.

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.

LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			U3	REVISED PER ECO—10—012730	20SEP10	HMR	MG



- 1 PARTS PACKAGED UNASSEMBLED.
- CABLE CLAMPING AREA ADJUSTABLE FROM .004 TO .055 SQ IN BY REVERSING CLAMPING INSERTS.
- 3 .329 MAXIMUM CABLE OUTSIDE DIAMETER.
- BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 400 ONLY.
- OBSOLETE PART NUMBER.
- STAINLESS STEEL (NON MAGNATIC).
- CABLE CLAMP WITH NON-MAGNETIC STAINLESS STEEL SCREWS.
- ZINC PLATED STEEL, NON-HEXAVALENT CHROMATE.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	BULK		.50±.00 .05	#5-20	1-206062-7
	INDIVIDUAL		.38±.00 .05	#5-20	1-206062-6
	BULK		.38±.00 .05	#5-20	1-206062-5
	INDIVIDUAL		.50±.00 .05	#5-20	1-206062-4
	INDIVIDUAL		.62±.00 .05	#5-20	1-206062-3
	INDIVIDUAL		.50±.00 .05	#5-20	1-206062-2
SUPERSEDED BY 1-206062-3	INDIVIDUAL		.62±.00 .05	#5-20	1-206062-1
OBSOLETE	SMALL PACK		.38±.00 .05	#5-20	1-206062-0
AMP BRAZIL USE ONLY	INDIVIDUAL		12mm ^{+.0} _{-.8}	3mm-20	206062-9
AMP BRAZIL USE ONLY	INDIVIDUAL		10mm ^{+.0} _{-.8}	3mm-20	206062-8
SUPERSEDED BY 1-206062-7	BULK		.50±.00 .05	#5-20	206062-4
SUPERSEDED BY 1-206062-4	INDIVIDUAL		.50±.00 .05	#5-20	206062-3
SUPERSEDED BY 1-206062-5	BULK		.38±.00 .05	#5-20	206062-2
SUPERSEDED BY 1-206062-6	INDIVIDUAL		.38±.00 .05	#5-20	206062-1
PACKAGING		SCREW FINISH	SCREW LENGTH	SCREW TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
THERMOPLASTIC

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN 4/29/91
A GRAFF

CHK 7-22-92
W.G.LENKER

APVD -

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

CABLE CLAMP KIT, STANDARD,
SHELL SIZE 11, CPC

SIZE A3
CAGE CODE 00779
DRAWING NO C-206062

RESTRICTED TO -

CUSTOMER DRAWING

SCALE NTS

SHEET 1 OF 1

REV U3