


*PANDUIT PART NUMBER	A IN (mm)	B IN (mm)	T IN (mm)	WEIGHT LBS / 100 FT (g)
T12T	.125 (3.2)	.218±.047 (5.5±1.2)	.020±.006 (0.5±0.2)	0.6 (272.2)
T19T	.188 (4.8)	.250±.047 (6.4±1.2)	.030±.008 (0.8±0.2)	1.3 (589.7)
T25T	.250 (6.4)	.375±.047 (9.5±1.2)	.030±.008 (0.8±0.2)	1.9 (861.8)
T38T	.375 (9.5)	.437±.047 (11.1±1.2)	.030±.010 (0.8±0.3)	2.8 (1270.0)
T50T	.500 (12.7)	.500±.047 (12.7±1.2)	.030±.016 (0.8±0.4)	4.1 (1859.7)
T62T	.625 (15.9)	.625±.047 (15.9±1.2)	.030±.020 (0.8±0.5)	5.0 (2267.9)
T75T	.750 (19.1)	.875±.047 (22.2±1.2)	.030±.020 (0.8±0.5)	6.3 (2857.6)
T100T	1.000 (25.4)	1.125±.047 (28.6±1.2)	.040±.020 (1.0±0.5)	11.4 (5158)

[illegible]